240W ◊ Input: 100-240VAC

RECOM AC/DC Converter

FEATURES

- Universal input voltage range 90-264VAC
- Built-In constant current circuit
- Two output variations 24V and 48V available
- Adjustable output voltage range ±10%
- High power density with efficiency up to 90.5%
- Temperature range -30°C to +70°C
- Cold start capability -40°C
- Reduced no load power consumption <0.3W
- Width only 40mm
- Low weight only 620g
- 3 years warranty



Dimensions (HxWxD): 123.6 x 40.0 x 116.8mm (4.86 x 1.57 x 4.6 inch) 620g (1.37 lbs)

APPLICATIONS











SAFETY & EMC















DESCRIPTION

The REDIIN240 DIN rail power supply series is designed for cost sensitive users to fulfill essential features, needed for many general industrial applications, without compromising on quality and reliability in the Basic Features Market segment. The REDIIN240 series delivers 240W output power in an extremely compact dimension of only 123.6 x 40.0 x 116.8mm. Two adjustable output variations from 24V to 48V are available. The convection-cooled units will operate full power from -30°C to +50°C (230VAC). It can operate in constant current mode, making it suitable for inductive and capacitive loads. The product is certified according to safety standards IEC/EN/UL 62368-1, IEC/EN/UL61010-1 and IEC/EN/UL/CSA61010-2-201. Electromagnetic radiated and conducted emissions are compliant to heavy industrial EN 61000-6-4 Class B Emission standard and EN 61000-6-2 Immunity standard. The product complies with environmental protection requirements as per RoHS Directive.

SELECTION GUIDE						
Part Number	Input Voltage Range [VAC]	Output Voltage nom. [VDC]	Output Adjustability [VDC]	Output Current max. [A]	Efficiency ⁽¹⁾ typ. [%]	Output Power max. [W]
REDIIN240-24	90-264	24	21.6-26.4	10	90	240
REDIIN240-48	90-264	48	43.2-52.8	5	90.5	240

Note1: Efficiency is tested at nominal input (230VAC) and full load at +25°C ambient

240W ◊ Input: 100-240VAC




BASIC CHARACTERISTICS (measured @ T _{AMB} = 25°C, nom. V _{IN} , full load and after warm-up unless otherwise stated)						
Parameter	Condition		Min.	Тур.	Max.	
Nominal Input Voltage	50/6	0Hz	100VAC		240VAC	
Operating Range (2)	47-6	3Hz	90VAC		264VAC	
Input Current	115	VAC		2.5A		
Input Current	230	VAC		1.3A		
Inrush Current	230VAC,	cold start			40A	
No Lood Dower Consumption	REDIIN2	240-24			210mW	
No Load Power Consumption	REDIIN2			300mW		
Input Frequency Range		47Hz		63Hz		
	REDIIN2	21.6VDC		26.4VDC		
Output Adjustability (3)	REDIIN2	43.2VDC		52.8VDC		
Power Factor	115/230VAC			0.95		
Start-up time	115/230VAC			500ms		
Rise time	115/230VAC			30ms		
Hold-up time	115/230VAC			20ms		
Periodic and Random Deviation PARD (4)	DEDUNO 40, 04	0°C to 70°C			150mVp-p	
	REDIIN240-24	-30°C to 0°C			450mVp-p	
	DEDUNO40 40	0°C to 70°C			200mVp-p	
	REDIIN240-48	-30°C to 0°C			600mVp-p	


Note2: The products were submitted for safety files at AC-Input operation.


Note3: Refer to "Adjust" in dimension drawing.


Note4: Measured at 20MHz bandwidth with an AC coupling mode, 5cm wires, 0.1µF MLCC and µf E-cap in parallel.

REDIIN240-24











240W ◊ Input: 100-240VAC





BASIC CHARACTERISTICS (measured @ T_{AMB}= 25°C, nom. V_{IN}, full load and after warm-up unless otherwise stated)

REDIIN240-48









REGULATIONS (measured @ T _{AMB} =)	25°C, nom. V _{IN} , full load and after w	arm-up unless otherwise stated)	
Parameter	Condition		Value
Output Accuracy			±1.0% max.
Line Regulation	low line to high	h line, full load	±0.5% max.
Load Regulation	0% to 100% load	REDIIN240-24	±0.5% max.
	0% to 100% load	REDIIN240-48	±0.5% max.
May Canacitive Load (start up)	REDIIN240-24		8000µF
Max. Capacitive Load (start-up)	REDIIN	240-48	3000µF
Transient Deenenee	115V/230VAC, 10-100% load		±10% typ.
Transient Response	recovery time (50% duty	y cycle @ 5Hz & 10kHz)	2.5A/µs

240W ♦ Input: 100-240VAC




PROTECTIONS (measured @ T _{AMB} = 25°C, nom. V _{IN} , full load and after warm-up unless otherwise stated)				
Parameter	Туре		Value	
Internal Input Fuse			T4AL/250V	
Short Circuit Protection (SCP)			hiccup mode, auto recovery	
Over Voltage Protection (OVD)	CELV output	REDIIN240-24	33.6VDC, latch off	
Over Voltage Protection (OVP)	SELV output	REDIIN240-48	64.8VDC, latch off	
Over Voltage Category (OVC)			OVC II	
Over Current Protection (OCP)	refer to "Over Current Protection"		105% - 150% of rated load current, auto recovery	
Over Temperature Protection (OTP)			latch off	
Class of Equipment			Class I with PE connection	
		I/P to O/P	3kVAC	
Isolation Voltage (safety certified) (5)	1 minute	I/P to PE	2kVAC	
		O/P to PE	1kVAC	
Leakage Current	240VAC/50Hz		0.75mA max.	
Power OK LED	normal mode, no protection activated		green light	

Note5: For repeat Hi-Pot testing, reduce the time and/or the test voltage

Over Current Protection

The unit operates in a constant voltage mode within its rated load range. When exceeding the maximum current rating by 105% to 150% of its nominal rating the unit enters into a limited-current mode which drives the output voltage to approximately 80% of its nominal set point. Further increased load leading the units into a hiccup mode with automated restart.



ENVIRONMENTAL (measured @ T _{AMB} = 25°C, nom. V _{IN} , full load and after warm-up unless otherwise stated)				
Parameter	Condition		Value	
Operating Ambient Temperature Range (7)	@ natural convection (0.1m/s)	with derating	-30°C to +70°C	
Operating Ambient Temperature hange	@ natural convection (0.11175)	full load	refer to "Derating Graph"	
Operating Altitude (6)			5000m	
Operating Humidity	non-condensing		20% - 95% RH max.	
Pollution Degree			PD2	
Shock	according to IEC 60068-2-27	operating	Half Sine Wave: 10G/11ms; 1 time in X axis	
SHOCK	according to IEC 60066-2-27	non-operating	Half Sine Wave: 50G/11ms; 3 time per direction, 9 times total	
Vibration	according to IFC COOCO 2 2C	operating	Sine Wave: 10Hz to 500Hz @ 19.6m/s² (2G peak); 10 min per cycle, 60 min for X direction	
Vibration according to IEC 60068-2-26	non-operating	Random: 5Hz to 500Hz; 2.09Grms; 20 min per axis for all X, Y, Z directions		
MTBF	according to telcordia SR	-332, 115/230VAC	700 x 10 ³ hours	

Note6: Recognized by safety agency for safe operation up to 5000m. High altitude operation may impact the performance and lifetime

240W ◊ Input: 100-240VAC




ENVIRONMENTAL (measured @ T_{AMB}= 25°C, nom. V_{IN}, full load and after warm-up unless otherwise stated)

Derating Graph

(@ Chamber and natural convection 0.1 m/s)

Note7: cold start capability -40°C; between -40°C and -30°C may exceed limits. Guaranteed start up above -30°C



SAFETY & CERTIFICATIONS		
Certificate Type (Safety)	Report Number	Standard
Audio/Video, information and communication technology equipment - Part1: Safety requirements (CB)		IEC62368-1:2014 2nd Edition
Audio/Video, information and communication technology equipment - Part1: Safety requirements	CN23AC4J-001	EN62368-1:2014 + A11:2017
Audio/Video, information and communication technology equipment - Part1: Safety requirements	E224736	UL62368-1:2014 CAN/CSA-C22.2 No. 62368-1:2014
Electrical Equipment For Measurement, Control, and Laboratory Use; Part 1: General Requirements (CB)	CN23338P-001	IEC61010-1:2010+A1:2016, 3rd Edition
Electrical Equipment For Measurement, Control, and Laboratory Use; Part 1: General Requirements	GN23330F-001	EN61010-1:2010+A1:2019
Electrical Equipment For Measurement, Control, and Laboratory Use; Part 1: General Requirements	E470721	UL61010-1, 3rd Edition, 2012-05-11 CSA C22.2 No. 61010-1, 3rd Ed. 2012-01-01
Electrical Equipment For Measurement, Control, and Laboratory Use; Part 2-201: Particular requirements for control equipment (CB Scheme)	ONIOCOCO COL	IEC61010-2-201:2017, 2nd Edition
Electrical Equipment For Measurement, Control, and Laboratory Use; Part 2-201: Particular requirements for control equipment	CN23338P-001	EN IEC 61010-2-201:2018
Electrical Equipment For Measurement, Control, and Laboratory Use; Part 2-201:	E470721	UL61010-2-201, 2nd Edition
Particular requirements for control equipment	E470721	CSA C22.2 No. 61010-2-201, 2nd Edition
RoHS2		RoHS 2011/65/EU + AM2015/863

EMC Compliance according to EN55032/35	Condition		Standard / Criterion
Electromagnetic compatibility of multimedia equipment - Emission requirements			EN55032:2015+A11:2020, Class B
Electromagnetic compatibility of multimedia equipment - Immunity requirements			EN55035:2017+A11:2020
ESD Electrostatic discharge immunity test (level 4)	Air: ±2, Contact	<i>'</i>	IEC61000-4-2:2008 , Criteria A EN61000-4-2:2009, Criteria A
Radiated, radio-frequency, electromagnetic field immunity test (level 2)	3V/m (80- 3V/m (1800, 2600	′	IEC/EN61000-4-3:2006+A2:2010, Criteria A
Fast Transient and Burst Immunity (level 3)	AC Power Port: L, N, PE, L-N-PE: 1kV		IEC/EN61000-4-4:2012, Criteria A
Surge Immunity (level 4)	AC Power Port: L-N: 0.5, 1kV L-PE, N-PE: 0.5, 1, 2kV		IEC/EN61000-4-5:2014+A1:2017, Criteria A
Immunity to conducted disturbances, induced by radio-frequency fields (level 2)	3Vrms (0.15-30MHz) 3-1Vrms (10-30MHz) 1Vrms (30-80MHz)		IEC61000-4-6:2013, Criteria A EN61000-4-6:2014, Criteria A
Power Magnetic Field Immunity (level 2)	1A/m 50Hz		IEC61000-4-8:2009, Criteria A EN61000-4-8:2010, Criteria A
Voltage Dips	100/230/240VAC, 50Hz	>95%, 0.5 cycles; 30%, 25 cycles	IEC/EN61000-4-11:2004+A1:2017, Criteria A

240W ◊ Input: 100-240VAC



210W V IIIput: 100 210W10				AG/BG GONVERTER
SAFETY & CERTIFICATIONS				
Voltage Interruptions	100/230/240VAC, 50Hz	>95% 250 cyc		IEC/EN61000-4-11:2004+A1:2017 Criteria E
Limits of Harmonic Current Emissions	meets standard	up to 100W P	OUT	EN IEC 61000-3-2:2019
Limits of Voltage Fluctuations & Flicker				EN61000-3-3:2013+A1:2019
EMC Compliance according to EN61204-3	Cond	lition		Standard / Criterion
Low voltage power supplies, d.c. output Part 3: Electromagnetic compatibility				EN61204-3:2000, Class A
ESD Electrostatic discharge immunity test	Air: ±2 Contact:	, 4, 8kV ±2, 4kV		IEC61000-4-2:2008, Criteria A EN61000-4-2:2009, Criteria A
Radiated, radio-frequency, electromagnetic field immunity test	3V/m (80-1000M	Hz, 895-905N	ЛHz)	IEC/EN61000-4-3:2006+A2:2010, Criteria A
Fast Transient and Burst Immunity	AC Power Port: L,	N, PE, L-N-PE	: 1kV	IEC/EN61000-4-4:2012, Criteria A
Surge Immunity	AC Power Port AC Power Port: L-P			IEC/EN61000-4-5:2014+A1:2017 Criteria A
Immunity to conducted disturbances, induced by radio-frequency fields	3Vrms (0.	15-80MHz)		IEC61000-4-6:2013, Criteria A EN61000-4-6:2014, Criteria A
	100VAC, 50H	30	0%	IEC/EN61000-4-11:2004+A1:2017, Criteria A
Voltage Dips	1000AG, 50H	60	0%	IEC/EN61000-4-11:2004+A1:2017, Criteria B
	230/240VAC, 5	OHz 30%	, 60%	IEC/EN61000-4-11:2004+A1:2017, Criteria A
Voltage Interruptions	100/230/240VAC,	50Hz >9	15%	IEC/EN61000-4-11:2004+A1:2017, Criteria E
Limits of Harmonic Current Emissions				EN IEC 61000-3-2:2019
Limits of Voltage Fluctuations & Flicker				EN61000-3-3:2013+A1:2017
EMC Compliance according to IEC/EN61000-6-4/6-2	Cond	lition		Standard / Criterion
Electromagnetic compatibility (EMC) - Part 6-4: Generic standards - Emission standard for industrial environments				IEC61000-6-4:2006+A1:2010 EN61000-6-4:2007+A1:2011
Electromagnetic compatibility (EMC) - Part 6-2: Generic standards - Immunity standard for industrial environments				IEC/EN61000-6-2:2005
ESD Electrostatic discharge immunity test	Contact: ±	I, 8, 15kV 2, 4, 6, 8kV -1000MHz)		IEC61000-4-2:2008, Criteria A EN61000-4-2:2009, Criteria A
Radiated, radio-frequency, electromagnetic field immunity test	3V/m (1400)-2000MHz))-2700MHz)		IEC/EN61000-4-3:2006+A2:2010, Criteria A
Fast Transient and Burst Immunity	AC Power Port: L,	N, PE, L-N-PE	: 2kV	IEC/EN61000-4-4:2012 Criteria A
Surge Immunity	AC Power Port I L-PE, N-PE:	N: 0.5, 1, 2k 0.5, 1, 2, 4kV	:V;	IEC/EN61000-4-5:2014+A1:2017, Criteria A
Immunity to conducted disturbances, induced by radio-frequency fields	10Vrms (0.	15-80MHz)		IEC61000-4-6:2013, Criteria <i>P</i> EN61000-4-6:2014, Criteria <i>P</i>
Power Magnetic Field Immunity	30A/m, 50/60Hz			IEC61000-4-8:2009, Criteria <i>A</i> EN61000-4-8:2010, Criteria <i>A</i>
		100%, 1 c	ycle	IEC61000-4-11:2004+A1:2017, Criteria A
Valtaga Dine	100VAC, 50Hz	60%, 10 cy 30%, 25 c		IEC61000-4-11:2004+A1:2017, Criteria E
Voltage Dips	230/240VAC, 50Hz	100%, 1 cy 60%, 10 cy 30%, 25 c	cles;	IEC61000-4-11:2004+A1:2017, Criteria A
Voltage Interruptions	100/230/240VAC, 50Hz	100%, 250	cycles	IEC/EN61000-4-11:2004+A1:2017 Criteria E
Limits of Harmonic Current Emissions				EN IEC 61000-3-2:2019
Limits of Voltage Fluctuations & Flicker				EN61000-3-3:2013+A1:2017

240W ◊ Input: 100-240VAC



DIMENSION & PHYSICAL CHARACTERISTICS			
Parameter	Туре	Value	
Material	chassis	aluminum	
Dimension (LbM/cD)		123.6 x 40.0 x 116.8mm	
Dimension (HxWxD)		4.86 x 1.57 x 4.6 inch	
Woight	with mounting clip	620g	
Weight	with mounting clip	1.37 lbs	

Dimension Drawing (mm) 123.4 116.8 117.2 40.0 **0.0.0** Adjust 📵 **(((** DC OK⊕ 123.6 (8.2)

Use flexible (stranded wire) or solid cables with the following wire cross-section is recommended.

Ferrules are required for flexible cables.

Use copper conductors designed for an operating temperature of at least 105°C.

Screw Terminal Information

Function	AWG	mm²	Tightening Torque	
VAC in L	18-12	0.8-3.3	0.6-0.8Nm	
VAC in N	18-12	0.8-3.3	0.6-0.8Nm	
PE 🚇	18-12	0.8-3.3	0.6-0.8Nm	
-Vout	18-12	0.8-3.3	0.4Nm	
+Vout	18-12	0.8-3.3	0.4Nm	
Wire stripping length: 7mm				

Tolerance: ±0.5mm


240W ◊ Input: 100-240VAC




INSTALLATION & APPLICATION


Mounting Instruction


Mounting Rail: Standard TS35 DIN Rail in accordance with EN 60715





Release






240W ◊ Input: 100-240VAC




INSTALLATION & APPLICATION

Multiple Mounting



Note8: To guarantee sufficient convection cooling, keep a distance of 40mm above and 20mm below the device. For vertical mounting the device should be installed with the input terminal on the bottom.

BLOCK DIAGRAM



PACKAGING INFORMATION				
Parameter	Туре	Value		
Packaging Dimension (LxWxH)	cardboard box	505.0 x 305.0 x 226.0mm		
Packaging Quantity		9pcs		
Storage Temperature Range		-40°C to +85°C		
Storage Humidity	non-condensing	10% - 95% RH max.		

The product information and specifications may be subject to changes even without prior written notice. The product has been designed for various applications; its suitability lies in the responsibility of each customer. The products are not authorized for use in safety-critical applications without RECOM's explicit written consent. A safety-critical application is an application where a failure may reasonably be expected to endanger or cause loss of life, inflict bodily harm or damage property. The applicant shall indemnify and hold harmless RECOM, its affiliated companies and its representatives against any damage claims in connection with the unauthorized use of RECOM products in such safety-critical applications.