

# Features

# Regulated Converters

- Compact 10.35 x 7.5mm SMD package
- Low profile (2.5mm)
- 3kVDC/1min isolation
- Low EMI emissions
- Ultra-wide temperature range -40°C to +125°C
- Fully automated, high-reliability design
- Semi-regulated 5V output



# RxxC05TExxS

**0.5 Watt**  
**16-Pin SOIC**  
**Single Output**



IEC/EN62368-1 3rd Edition certified  
 CB Report

## Description

The R05C05TE05S is a low cost, low profile, 0.5W SMD isolated DC/DC single output converter with 4.5-5.5V input range and a semi-regulated 5V output. There is no minimum load requirement which is ideal for applications which switch into very light load operation modes. The device is also able to deliver a 600mW for applications requiring additional power for short peak operation modes. Standard isolation is 3kVDC/1min, and the operating temperature is from -40°C up to +125°C with derating. The fully-automated design which is equipped with short-circuit, over-current, and over-temperature protection ensures the highest reliability in applications such as communication, current sensing, and COM port isolation.

## Selection Guide

Part Number	Input Voltage Range [VDC]	Output Voltage [VDC]	Output Power [W]	Efficiency typ. <sup>(1)</sup> [%]
R05C05TE05S	4.5-5.5	5	0.5	53

### Notes:

Note1: nom.  $V_{IN}$  = 5VDC,  $V_{OUT}$  = 5VDC, full load

## Model Numbering



### Notes:

Note2: add suffix “-R” for standard tape and reel packaging

add suffix “-CT” for bag packaging for more details refer to “PACKAGING INFORMATION”

## Specifications (measured @ $T_a$ = 25°C, nom. $V_{in}$ , full load and after warm-up unless otherwise stated)

ABSOLUTE MAXIMUM RATINGS <sup>(3)</sup>				
Parameter	Condition	Min.	Typ.	Max.
Absolute Maximum Voltage	$+V_{IN}$ to $-V_{IN}$	-0.3VDC		6VDC
	$+V_{IN}$ to $-V_{IN}$ or $SGND_{IN}$	-0.3VDC		6VDC
	$+V_{OUT}$ to $-V_{OUT}$ or $SGND_{OUT}$	-0.3VDC		6VDC
Operating IC Junction Temperature ( $T_J$ )				+150°C
Lead Temperature				+260°C
Storage Temperature ( $T_{STO}$ )		-65°C		+150°C


### Notes:

Note3: Stresses beyond those listed under absolute maximum ratings can cause permanent damage to the device. (Values are at non-operating)

**Specifications** (measured @ Ta= 25°C, nom. Vin, full load and after warm-up unless otherwise stated)

BASIC CHARACTERISTICS				
Parameter	Condition	Min.	Typ.	Max.
Input Voltage Range		4.5VDC	5VDC	5.5VDC
Under Voltage Lockout (UVLO)	DC-DC ON		3.28VDC	
	DC-DC OFF		2.88VDC	
Under Voltage Lockout Hysteresis			190mV	
Input Current Range	P <sub>OUT</sub> = 0.5W		240mA	
	P <sub>OUT</sub> = 0.6W		255mA	
Quiescent Current			7mA	
Minimum Load		0%		
Internal Operating Frequency			30MHz	
Output Ripple Voltage			50mVp-p	100mVp-p

**Typical Application Circuit**




**Input and Output Capacitors\***

C <sub>1</sub>	C <sub>2</sub>	C <sub>3</sub>	C <sub>4</sub>
10µF	0.1µF	10µF	0.1µF

\*these capacitors are mandatory for stable operation

**Efficiency vs. Load**



REGULATION				
Parameter	Condition	Min.	Typ.	Max.
Output Voltage Accuracy	V <sub>IN</sub> = 4.5-5.5VDC, load= 0A		±1.5%	
Line Regulation	V <sub>IN</sub> = 4.5-5.5VDC, load= 0.12A		±0.5%	
Load Regulation	0% - 100% load		1.0%	

**Specifications** (measured @ Ta= 25°C, nom. Vin, full load and after warm-up unless otherwise stated)

**PROTECTIONS**

Parameter	Condition	Values
Short Circuit Protection (SCP)		continuous , hiccup mode
Over Current Protection		220mA, hiccup mode
Over Temperature Protection		automatic restart after cool down
Thermal Shutdown	IC junction temperature	+160°C
	hysteresis	+20°C
Isolation Voltage	tested for 1second	3.6kVDC
	rated for 1 minute	3kVDC
Isolation Resistance	V <sub>ISO</sub> = 500VDC, 25°C	50GΩ typ.
Isolation Capacitance		7pF typ.
Isolation Grade	according to 62368-1	functional
External Clearance		>8mm
External Creepage		>8mm

**ENVIRONMENTAL**


Parameter	Condition	Value
Operating Temperature Range	@ natural convection 0.1m/s	-40°C to +125°C
	with derating	
ESD	human-body model (HBM), ANSI/ESDA/JEDEC JS-001	±6.0kV
	charged-device model (CDM), JEDEC JESD22-C101	±2.0kV
Moisture Sensitive Level	MSL peak temp. <sup>(5)</sup>	Level 3, 260°C, 168hrs
Thermal Impedance <sup>(6)</sup>	junction to T <sub>AMB</sub>	63.8K/W
	junction to case (top)	21.4K/W
	junction to case (bottom)	37.2K/W
	junction to board	38.5K/W

**Notes:**

Note5: The Moisture Sensitivity Level rating according to the JEDEC industry standard classifications, and peak solder temperature


Note6: Tested with 54.0 x 85.6mm 2 layer PCB with 105µm copper

**Peak Load Capability**



- P<sub>nom</sub> = nom. output power (0.5W) [W]
- P<sub>p</sub> = peak output power (≤0.6W) [W]
- t<sub>1</sub> = peak time set (60s max.) [s]
- t<sub>2</sub> = recovery time (min. 3 x t<sub>1</sub>) [s]

**Thermal Derating <sup>(6)</sup>**



**Specifications** (measured @ Ta= 25°C, nom. Vin, full load and after warm-up unless otherwise stated)





**SAFETY AND CERTIFICATIONS**

Certificate Type (Safety)	Report Number	Standard
Information Technology Equipment, General Requirements for Safety (CB Scheme)	DK-139515-A1-UL	IEC62368-1:2018, 3rd Edition
Information Technology Equipment, General Requirements for Safety	S20230116152501	EN IEC 62368-1:2020 + A11:2020
RoHS2		RoHS 2011/65/EU + AM2015/863

**DIMENSION AND PHYSICAL CHARACTERISTICS**

Parameter	Type	Value
Dimension (LxWxH)		10.35 x 7.5 x 2.50mm
Weight		0.1g typ.


Dimension Drawing (mm)



**Pin Information**


Pad #	Function
1,2	-VIN
3,4	+VIN
5,6,7,8	SGND <sub>IN</sub>
9,11,12	SGND <sub>OUT</sub>
10	DNC (do not connect)
13,14	+V <sub>OUT</sub>
15,16	-V <sub>OUT</sub>

Tolerances: x.x= ±0.1mm  
x.xx= ±0.05mm



**Specifications** (measured @ Ta= 25°C, nom. Vin, full load and after warm-up unless otherwise stated)

**Footprint Details**



**PACKAGING INFORMATION**

Parameter	Type	Value
Packaging Dimension (LxWxH)	reel (diameter + width)	Ø177.8 + 24.4mm height
	tape and reel (carton)	260.0 x 240.0 x 60.0mm
	moisture barrier bag ("-CT")	100.0 x 100.0 x 30mm
Tape Width		24mm
Packaging Quantity	tape and reel	500pcs
	moisture barrier bag ("-CT")	10pcs
Storage Temperature Range		-65°C to +150°C

The product information and specifications may be subject to changes even without prior written notice. The product has been designed for various applications; its suitability lies in the responsibility of each customer. The product is not authorized for use in safety-critical applications without RECOM's explicit written consent. A safety-critical application is an application where a failure may reasonably be expected to endanger or cause loss of life, inflict bodily harm or damage property. The applicant shall indemnify and hold harmless RECOM, its affiliated companies and its representatives against any damage claims in connection with the unauthorized use of RECOM products in such safety-critical applications.