


PRODUCT FEATURES

- Small-Sized Isolation Transformer
- SMD Surface Mount Installation
- Isolation Voltage: 1500VDC/1minute
- Storage Temperature: -40~125°C
- Operating Temperature (Ambient Temperature + Temperature Rise): -40~125°C
- Reflow Soldering Temperature: Peak Temperature $\leq 245^{\circ}\text{C}$ (10s)
- Number of Reflow Soldering Cycles: Recommended not to exceed 2 times
- Maximum Product Dimensions (MAX): 13.0mm \times 11.5mm \times 5.9mm


DIMENSIONS AND SCHEMATIC DIAGRAM [mm]



PRODUCT MARKING

Pin1	
Marking	Company Logo
	Product Model

RECOMMENDED LAND PATTERN [mm]



ELECTRICAL PROPERTIES

Properties		Test Conditions	Value	Unit	Tol.
Inductance	L	1-3	48.6	μ H	Typ
Turns Ratio	n	N1:N2:N3:N4	1:3.6:2.4:1		
DC Resistance 1	R_{DC1}	1-3	0.32	Ω	Max
DC Resistance 2	R_{DC2}	2-4	0.45	Ω	Max
DC Resistance 3	R_{DC3}	5-7	0.06	Ω	Max
DC Resistance 4	R_{DC4}	6-8	0.08	Ω	Max
Leakage Inductance	L_S	1-3	0.8	μ H	Max
Insulation Test Voltage	V_T	N2,3:N1,4/60s/1mA	1500	V(DC)	1min.

GENERAL INFORMATION

Operating Temperature	-40~125°C
Storage Conditions (in original packaging)	<40°C/<75%RH
Moisture Sensitivity Level (MSL)	1
Electrical Specifications @ 25°C unless otherwise noted	

MATERIAL CERTIFICATION

ITEM		UL NO
1	BOBBIN	E41429
2	WIRE	E253843
3	TAPE	E165111
4	GLUE	E218090

CERTIFICATION

RoHS Approval	Compliant [2011/65/EU&2015/863]
REACH Approval	Conform or declared [(EC)1907/2006]
Halogen Free	Conform [EN 14582:2016]

TYPICAL APPLICATION


Input Voltage	V_{IN}	18-75	V(DC)
Output Voltage 1	V_{OUT1}	5	V(DC)
Output Current 1	I_{OUT1}	1200	mA
Switching Frequency	f_{switch}	330	kHz

Input: N2


Output 1: N1/N4

Table and graph show a typical application. Values may vary by application.

REFERENCE CIRCUIT DIAGRAM




Typical Curve:





PACKAGING SPECIFICATION - TAPE [mm]

ITRM	W	A0	B0	K0	K1	P	F	E	D0	D1	P0	P2	T
DIM	24.00	11.50	13.10	6.10	--	16.00	11.50	1.75	1.50	--	4.00	2.00	0.40
TOLE	+0.30 -0.30	+0.15 -0.15	+0.15 -0.15	+0.10 -0.10	+0.10 -0.10	+0.10 -0.10	+0.10 -0.10	+0.10 -0.10	+0.10 -0.00	+0.10 -0.00	+0.10 -0.10	+0.15 -0.15	+0.05 -0.05




Reel [mm]



		✓			
SPEC	16	24	32	44	56
DIM A" ± 0.5	16.5	24.5	32.5	44.5	56.5
DIM B" ± 0.3	2.10	2.10	2.10	2.10	2.10
DIM C" ± 0.5	100	100	100	100	100

CLASSIFICATION REFLOW PROFILE FOR SMT COMPONENTS



Profile Feature		Value
Preheat Temperature Min	$T_{s\ min}$	150°C
Preheat Temperature Max	$T_{s\ max}$	200°C
Preheat Time t_s from $T_{s\ min}$ to $T_{s\ max}$	t_s	100 seconds
Ramp-up Rate (T_L to T_p)		3°C/second max.
Liquidous Temperature	T_L	217°C
Time t_L maintained above T_L	t_L	100 seconds
Peak package body temperature	T_p	$T_p \leq T_c$, see Table below
Time within 5°C of actual peak temperature	t_p	30 seconds
Ramp-down Rate (TP to TL)		6°C/second max.
Time 25°C to peak temperature		5 minutes max.

Refer to IPC/JEDEC J-STD-020F

PACKAGE CLASSIFICATION REFLOW TEMPERATURE (T_p)

Properties	Volume mm ³ <350	Volume mm ³ 350-2000	Volume mm ³ >2000
PB-Free Assembly/Package Thickness < 1.6 mm	260 °C	260 °C	260 °C
PB-Free Assembly/Package Thickness 1.6 mm - 2.5 mm	260 °C	250 °C	245 °C
PB-Free Assembly/Package Thickness > 2.5 mm	250 °C	245 °C	245 °C

Refer to IPC/JEDEC J-STD-020F

ORDER INFORMATION

Order Code	Marking Code*	Weight (g/pcs)	Package Type	Quantity (pcs/Reel)
RBE-027-UH5S-R	RBE-027	1.396g	Tape & Reel	500pcs

*Marking Code

RBE027—— Product Code

The product information and specifications may be subject to changes even without prior written notice. The product has been designed for various applications; its suitability lies in the responsibility of each customer. The products are not authorized for use in safety-critical applications without RECOM's explicit written consent. A safety-critical application is an application where a failure may reasonably be expected to endanger or cause loss of life, inflict bodily harm or damage property. The applicant shall indemnify and hold harmless RECOM, its affiliated companies and its representatives against any damage claims in connection with the unauthorized use of RECOM products in such safety-critical applications.