480W ◊ Input: 100-240VAC

### RECOM AC/DC Converter

### **FEATURES**

- Universal input voltage range 90-264VAC
- Built-In constant current circuit
- Power Factor >0.96 115VAC & >0.93 230VAC
- Two adjustable output variations 24-28V & 48-55V
- High power density with efficiency up to 93.5%
- Temperature range -30°C to +70°C
- Cold start capability -40°C
- Reduced no load power consumption <0.75W</li>
- Width only 56mm
- Low weight only 870g
- 3 years warranty



Dimensions (HxWxD): 123.6 x 56.0 x 116.8mm (4.86 x 2.2 x 4.6 inch) 870g (1.92 lbs)

#### **APPLICATIONS**











#### **SAFETY & EMC**















#### DESCRIPTION

The REDIIN480 DIN rail power supply series is designed for cost sensitive users to fulfill essential features, needed for many general industrial applications, without compromising on quality and reliability in the Basic Features Market segment. The REDIIN480 series delivers 480W output power in an extremely compact dimension of only  $123.6 \times 56.0 \times 116.8 \text{mm}$ . Two adjustable output variations from 24V to 48V are available. The convection-cooled units will operate full power from -30°C to +50°C (230VAC). It can operate in constant current mode, making it suitable for inductive and capacitive loads. The product is certified according to safety standards IEC/EN/UL 62368-1, IEC/EN/UL61010-1 and IEC/EN/UL/CSA61010-2-201. Electromagnetic radiated and conducted emissions are compliant to heavy industrial EN 61000-6-4 Class B Emission standard and EN 61000-6-2 Immunity standard. The product complies with environmental protection requirements as per RoHS Directive.

SELECTION GUIDE						
Part Number	Input Voltage Range	Output Voltage nom.	Output Adjustability	Output Current max.	Efficiency <sup>(1)</sup> typ.	Output Power max.
Number	[VAC]	[VDC]	[VDC]	[A]	[%]	[W]
REDIIN480-24	90-264	24	24-28	20	93	480
REDIIN480-48	90-264	48	48-55	10	93.5	480

Note1: Efficiency is tested at nominal input (230VAC) and full load at +25°C ambient

480W ◊ Input: 100-240VAC




BASIC CHARACTERISTICS (measured @	T <sub>AMB</sub> = 25°C, nom. V <sub>IN</sub> , full lo	oad and after warm-up unless ot	herwise stated)		
Parameter	Condition			Тур.	Max.
Nominal Input Voltage	Į	50/60Hz	100VAC		240VAC
Operating Range (2)	4	47-63Hz	90VAC		264VAC
Input Current		115VAC		4.7A	
Input Current —		230VAC		2.4A	
Inrush Current	230V	AC, cold start			40A
No Load Power Consumption	11	5/230VAC			750mW
Input Frequency Range			47Hz		63Hz
Output Adinatability (3)	REDIIN480-24				28VDC
Output Adjustability (3)	REDIIN480-48				55VDC
Power Factor	115VAC			0.96	
Power Factor	230VAC			0.93	
Ctart up time	115/000///0	REDIIN480-24		500ms	
Start-up time	115/230VAC	REDIIN480-48		800ms	
Rise time	115/230VAC			30ms	
Hold-up time	115/230VAC			25ms	
	REDIIN480-24	0°C to 70°C			150mVp-p
Periodic and Random Deviation PARD (4)		-30°C to 0°C			450mVp-p
Periodic and Kandom Deviation PARD (*)	DEDIIN/400 //0	0°C to 70°C			200mVp-p
	REDIIN480-48	-30°C to 0°C			600mVp-p


Note2: The products were submitted for safety files at AC-Input operation.

Note3: Refer to "Adjust" in dimension drawing.

Note4: Measured at 20MHz bandwidth with an AC coupling mode, 5cm wires, 0.1µF MLCC and µf E-cap in parallel.

### **REDIIN480-24**







480W ◊ Input: 100-240VAC



BASIC CHARACTERISTICS (measured @ T<sub>AMB</sub>= 25°C, nom. V<sub>IN</sub>, full load and after warm-up unless otherwise stated)

### REDIIN480-24





REGULATIONS (measured @ T <sub>AMB</sub> = 25°C, nom. V <sub>IN</sub> , full load and after warm-up unless otherwise stated)			
Parameter	Condition	Value	
Output Accuracy		±1.0% max.	
Line Regulation	low line to high line, full load	±0.5% max.	
Load Regulation	0% to 100% load	±0.5% max.	
May Canasitiva Land (start up)	REDIIN480-24	8000µF	
Max. Capacitive Load (start-up)	REDIIN480-48	3000µF	
Transiant Dagnana	115V/230VAC, 10-100% load	±10% typ.	
Transient Response	recovery time (50% duty cycle @ 5Hz & 10kHz)	2.5A/µs	

PROTECTIONS (measured @ T <sub>AMB</sub> =	25°C, nom. V <sub>IN</sub> , full load an	d after warm-up unless otherwis	e stated)
Parameter		Туре	Value
Internal Input Fuse			F10AH/250V
Short Circuit Protection (SCP)			hiccup mode, auto recovery
Over Voltage Protection (OVP)	CELV output	REDIIN480-24	34VDC, latch off
Over Voltage Protection (OVP)	SELV output	REDIIN480-48	68VDC, latch off
Over Voltage Category (OVC)			OVC II
Over Current Protection (OCP)	refer to "Over Current Protection"		105% - 150% of rated load current, auto recovery
Over Temperature Protection (OTP)			latch off
Class of Equipment			Class I with PE connection
		I/P to O/P	3kVAC
Isolation Voltage (safety certified) (5)	1 minute	I/P to PE	2kVAC
		O/P to PE	1kVAC
Leakage Current	2	240VAC/50Hz	1.5mA max.
Power OK LED	normal mode, no protection activated		green light

Note5: For repeat Hi-Pot testing, reduce the time and/or the test voltage


480W ◊ Input: 100-240VAC



PROTECTIONS (measured @ T<sub>AMB</sub>= 25°C, nom. V<sub>IN</sub>, full load and after warm-up unless otherwise stated)

**Over Current Protection** 

The unit operates in a constant voltage mode within its rated load range. When exceeding the maximum current rating by 105% to 150% of its nominal rating the unit enters into a limited-current mode which drives the output voltage to approximately 80% of its nominal set point. Further increased load leading the units into a hiccup mode with automated restart.




ENVIRONMENTAL (measured @ T <sub>AMB</sub> = 25°C, nom. V <sub>IN</sub> , full load and after warm-up unless otherwise stated)				
Parameter	Condition		Value	
Operating Ambient Temperature Range (7)	@ natural convection (0.1m/s)	with derating	-30°C to +70°C	
Operating Ambient Temperature hange	@ natural convection (0.11175)	full load	refer to "Derating Graph"	
Operating Altitude (6)			5000m	
Operating Humidity	non-condensing		20% - 90% RH max.	
Pollution Degree			PD2	
Charle	according to IEC 60068-2-27	operating	Half Sine Wave: 10G/11ms; 1 time in X axis	
Shock		non-operating	Half Sine Wave: 50G/11ms; 3 time per direction, 9 times total	
		operating	Sine Wave: 10Hz to 500Hz @ 19.6m/s² (2G peak);	
Vibration	according to IEC 60068-2-26	operating	10 min per cycle, 60 min for X direction	
		non-operating	Random: 5Hz to 500Hz; 2.09Grms;	
	non-operatin		20 min per axis for all X, Y, Z directions	
MTBF	according to telcordia SR-332, 115/230VAC		700 x 10 <sup>3</sup> hours	

Note6: Recognized by safety agency for safe operation up to 5000m. High altitude operation may impact the performance and lifetime

### **Derating Graph**

(@ Chamber and natural convection 0.1 m/s)

Note7: cold start capability -40°C; between -40°C and -30°C may exceed limits. Guaranteed start up above -30°C



480W ◊ Input: 100-240VAC



SAFETY & CERTIFICATIONS				
Certificate Type (Safety)		Repo	rt Number	Standard
Audio/Video, information and communication technology equipment - Part1: Safety requirements (CB)		CN23FXWD-001		IEC62368-1:2014 2nd Edition
Audio/Video, information and communication technology equipment - Part1: Safety requirements		0.120	.,,,,,,	EN62368-1:2014 + A11:2017
Audio/Video, information and communication technology equipment - Part1: Safety		E2	224736	UL62368-1:2014 CAN/CSA-C22.2 No. 62368-1:2014
Electrical Equipment For Measurement, Control, and Laboratory Use; Part 1: General		1	91-D1020-	IEC61010-1:2010+A1:2016, 3rd Edition
Electrical Equipment For Measurement, Control, and Laboratory Use; Part 1: General	al Requirements	1-A	0-C0-CB	EN61010-1:2010+A1:2019
Electrical Equipment For Measurement, Control, and Laboratory Use; Part 1: General	al Requirements	E4	470721	UL61010-1, 3rd Edition, 2012-05-11 CSA C22.2 No. 61010-1, 3rd Ed. 2012-01-01
Electrical Equipment For Measurement, Control, and Laboratory Use; Part 2-201: Particular requirements for control equipment (CB Scheme)		E3389	991-D1020-	IEC61010-2-201:2017, 2nd Edition
Electrical Equipment For Measurement, Control, and Laboratory Use; Part 2-201: Particular requirements for control equipment		1-A	.0-C0-CB	EN IEC 61010-2-201:2018
Electrical Equipment For Measurement, Control, and Laboratory Use; Part 2-201: Particular requirements for control equipment		E4	470721	UL61010-2-201, 2nd Edition CSA C22.2 No. 61010-2-201, 2nd Edition
RoHS2				RoHS 2011/65/EU + AM2015/863
EMC Compliance according to EN55032/35	Cond	lition		Standard / Criterion
Electromagnetic compatibility of multimedia equipment - Emission requirements	Conc			EN55032:2015+A11:2020, Class B
Electromagnetic compatibility of multimedia equipment - Immunity requirements				EN55035:2017+A11:2020
	Air: ±2, 4	, 8, 15k	⟨V	IEC61000-4-2:2008 , Criteria A
ESD Electrostatic discharge immunity test (level 4)		±2, 4, 6, 8kV		EN61000-4-2:2009, Criteria A
Radiated, radio-frequency, electromagnetic field immunity test (level 2)	,	0-1000MHz) 00, 3500, 5000MHz)		IEC/EN61000-4-3:2006+A2:2010, Criteria A
Fast Transient and Burst Immunity (level 3)		Port: L, N, PE, L-N-PE: 1kV		IEC/EN61000-4-4:2012, Criteria A
Surge Immunity (level 4)	AC Power Port: L L-PE, N-PE: (			IEC/EN61000-4-5:2014+A1:2017, Criteria A
Immunity to conducted disturbances, induced by radio-frequency fields (level 2)	3Vrms (0.1 nunity to conducted disturbances, induced by radio-frequency fields (level 2) 3-1Vrms (10.1 1Vrms (30.1		IHz)	IEC61000-4-6:2013, Criteria A EN61000-4-6:2014, Criteria A
Power Magnetic Field Immunity (level 2)		m 50Hz		IEC61000-4-8:2009, Criteria A EN61000-4-8:2010, Criteria A
Voltage Dips	100/230/240VAC, 50Hz		o, 0.5 cycles; o, 25 cycles	IEC/EN61000-4-11:2004+A1:2017, Criteria A
Voltage Interruptions	100/230/240VAC, 50Hz		>95%, 50 cycles	IEC/EN61000-4-11:2004+A1:2017, Criteria B
Limits of Harmonic Current Emissions	meets standard	up to 10	DOW Pout	EN IEC 61000-3-2:2019
Limits of Voltage Fluctuations & Flicker				EN61000-3-3:2013+A1:2019
EMC Compliance according to EN61204-3	Cond	lition		Standard / Criterion
Low voltage power supplies, d.c. output Part 3: Electromagnetic compatibility				EN61204-3:2000, Class A
ESD Electrostatic discharge immunity test	Air: ±2, 4, 8, 15kV Contact: ±2, 4, 6, 8kV			IEC61000-4-2:2008, Criteria A EN61000-4-2:2009, Criteria A
Radiated, radio-frequency, electromagnetic field immunity test			5-905MHz,	IEC/EN61000-4-3:2006+A2:2010, Criteria A
Fast Transient and Burst Immunity	AC Power Port: L, I			IEC/EN61000-4-4:2012, Criteria A
Surge Immunity	AC Power Port: AC Power Port: L-PE			IEC/EN61000-4-5:2014+A1:2017 Criteria A
Immunity to conducted disturbances, induced by radio-frequency fields			Hz)	IEC61000-4-6:2013, Criteria A EN61000-4-6:2014, Criteria A
Voltage Dips	100/230/240VAC,	50Hz	30%, 60%	IEC/EN61000-4-11:2004+A1:2017, Criteria A
Voltage Interruptions	100/230/240VAC,	50Hz	>95%	IEC/EN61000-4-11:2004+A1:2017, Criteria B
Limits of Harmonic Current Emissions				EN IEC 61000-3-2:2019
Limits of Voltage Fluctuations & Flicker				EN61000-3-3:2013+A1:2017

480W ◊ Input: 100-240VAC



SAFETY & CERTIFICATIONS			
EMC Compliance according to IEC/EN61000-6-4/6-2	Cond	lition	Standard / Criterion
Electromagnetic compatibility (EMC) - Part 6-4: Generic standards -			IEC61000-6-4:2006+A1:2010
Emission standard for industrial environments			EN61000-6-4:2007+A1:2011
Electromagnetic compatibility (EMC) - Part 6-2: Generic standards - Immunity standard for industrial environments			IEC/EN61000-6-2:2005
ESD Electrostatic discharge immunity test	Air: ±2, 4	l, 8, 15kV	IEC61000-4-2:2008, Criteria A
Libeliostatic discharge infindinty test	Contact: ±	2, 4, 6, 8kV	EN61000-4-2:2009, Criteria A
Radiated, radio-frequency, electromagnetic field immunity test	10V/m (80 3V/m (1400	-1000MHz) 0-6000MHz)	IEC/EN61000-4-3:2006+A2:2010, Criteria A
Fast Transient and Burst Immunity	AC Power Port: L,	N, PE, L-N-PE: 2kV	IEC/EN61000-4-4:2012 Criteria A
Surge Immunity	AC Power Port I L-PE, N-PE:	-N: 0.5, 1, 2kV; 0.5, 1, 2, 4kV	IEC/EN61000-4-5:2014+A1:2017, Criteria A
Immunity to conducted disturbances, induced by radio-frequency fields	10Vrma (0	15-80MHz)	IEC61000-4-6:2013, Criteria A
inimumity to conducted disturbances, induced by radio-frequency fields	10411115 (0.	13-601/1112)	EN61000-4-6:2014, Criteria A
Power Magnetic Field Immunity	30A/m, 50/60Hz		IEC61000-4-8:2009, Criteria A
Tower magnetic riela inimunity	30A(III,	30/00112	EN61000-4-8:2010, Criteria A
	100VAC, 50Hz	30%, 25/30 cycles; 100%, 1 cycle	IEC61000-4-11:2004+A1:2017, Criteria A
Voltage Dips		60%, 10/12 cycles	IEC61000-4-11:2004+A1:2017, Criteria B
voltage Dipo	230/240VAC, 50Hz	100%, 1 cycle; 60%, 10 cycles; 30%, 25 cycles	IEC61000-4-11:2004+A1:2017, Criteria A
Voltage Interruptions	100/230/240VAC,	100%,	IEC/EN61000-4-11:2004+A1:2017,
Voltage Interruptions	50Hz	250/300 cycles	Criteria B
Limits of Harmonic Current Emissions			EN IEC 61000-3-2:2019
Limits of Voltage Fluctuations & Flicker			EN61000-3-3:2013+A1:2017


DIMENSION & PHYSICAL CHARACTERISTICS			
Parameter	Туре	Value	
Material	chassis	aluminum	
Dimension (HxWxD)		123.6 x 56.0 x 116.8mm	
		4.86 x 2.2 x 4.6 inch	
Weight	with mounting clip	870g	
weight	with mounting clip	1.92 lbs	


480W ◊ Input: 100-240VAC



### **DIMENSION & PHYSICAL CHARACTERISTICS**

**Dimension Drawing (mm)** 





Use flexible (stranded wire) or solid cables with the following wire cross-section is recommended.

Ferrules are required for flexible cables.

Use copper conductors designed for an operating temperature of at least 105°C.

### **Screw Terminal Information**

Function	AWG	mm²	Tightening Torque	
VAC in L	14-12	2.1-3.3	0.6Nm	
VAC in N	14-12	2.1-3.3	0.6Nm	
PE 🚇	14-12	2.1-3.3	0.6Nm	
-Vout	14-12	2.1-3.3	0.4Nm	
+Vout	14-12	2.1-3.3	0.4Nm	
Wire stripping length: 8mm				

Tolerance: ±0.5mm


480W ◊ Input: 100-240VAC




### INSTALLATION & APPLICATION


### **Mounting Instruction**


Mounting Rail: Standard TS35 DIN Rail in accordance with EN 60715





Release






480W ◊ Input: 100-240VAC




### **INSTALLATION & APPLICATION**

#### **Multiple Mounting**



Note8: To guarantee sufficient convection cooling, keep a distance of 40mm above and 20mm below the device. For vertical mounting the device should be installed with the input terminal on the bottom.

### **BLOCK DIAGRAM**



PACKAGING INFORMATION			
Parameter	Туре	Value	
Packaging Dimension (LxWxH)	cardboard box	505.0 x 305.0 x 226.0mm	
Packaging Quantity		7pcs	
Storage Temperature Range		-40°C to +85°C	
Storage Humidity	non-condensing	5% - 95% RH max.	

The product information and specifications may be subject to changes even without prior written notice. The product has been designed for various applications; its suitability lies in the responsibility of each customer. The products are not authorized for use in safety-critical applications without RECOM's explicit written consent. A safety-critical application is an application where a failure may reasonably be expected to endanger or cause loss of life, inflict bodily harm or damage property. The applicant shall indemnify and hold harmless RECOM, its affiliated companies and its representatives against any damage claims in connection with the unauthorized use of RECOM products in such safety-critical applications.