


PRODUCT FEATURES

- Small-Sized Isolation Transformer
- Isolation Voltage: 1500VDC/1minute
- SMD (Surface Mount Device) Mounting
- Reflow Soldering Temperature: Peak Temperature $\leq 250^{\circ}\text{C}$ (10s)
- Recommended Reflow Soldering Times: No More Than 2 Times
- Product Volume: 8.1mm x 6.8mm x 3.8mm (MAX)


DIMENSIONS AND SCHEMATIC DIAGRAM [mm]



PRODUCT MARKING

Pin1	○
Marking	Company Logo
	Product Model

RECOMMENDED LAND PATTERN [mm]



ELECTRICAL PROPERTIES

Properties		Test Conditions	Value	Unit	Tol.
Inductance	L	N1/100kHz/0.1V	121	μH	min.
Turns Ratio	n	N1:N2:N3	1:1.12:1.12		
DC Resistance 1	R _{DC1}	N1/25°C	0.26	Ω	Max
DC Resistance 2	R _{DC2}	N2:N3 /25°C	0.27	Ω	Max
Voltage-μSecond	∫ Udt	N1/ bipolar waveform	10.3	Vμs	
Interwinding Capacitance	C _{VWV}	PIN1-6/100kHz/ 0.1V/25°C	18	pF	Max
Leakage Inductance	L _S	N1/100kHz/0.1V, all other terminals short	0.25	uH	Max
Insulation Test Voltage	V _T	N1: N2,3/60s/1mA	1500	V(DC)	1min.

GENERAL INFORMATION

Operating Temperature	-40~125°C
Storage Conditions (in original packaging)	<40°C/<75%RH
Moisture Sensitivity Level (MSL)	1
Electrical Specifications @ 25°C unless otherwise noted	

MATERIAL CERTIFICATION

ITEM		UL NO
1	CASE	E150608
2	WIRE	E253843
3	VARNISH	E314793

CERTIFICATION

RoHS Approval	Compliant [2011/65/EU&2015/863]
REACH Approval	Conform or declared [(EC)1907/2006]
Halogen Free	Conform [EN 14582:2016]

TYPICAL APPLICATION


Input Voltage	V _{IN}	5	V(DC)
Output Voltage 1	V _{OUT1}	5	V(DC)
Output Current 1	I _{OUT1}	200	mA
Switching Frequency	f _{switch}	340	kHz

Input : N1


Output 1: N2 / N3

Table and graph show a typical application. Values may vary by application.

REFERENCE CIRCUIT DIAGRAM




Typical Curve:




PACKAGING SPECIFICATION - TAPE [mm]


ITRM	W	A0	B0	K0	K1	P	F	E	D0	D1	P0	P2	T
DIM	24.00	7.10	8.20	3.75	--	12.00	11.50	1.75	1.50	--	4.00	2.00	0.40
TOLE	+0.30 -0.30	+0.15 -0.15	+0.15 -0.15	+0.10 -0.10	+0.10 -0.10	+0.10 -0.10	+0.10 -0.10	+0.10 -0.10	+0.10 -0.00	+0.10 -0.00	+0.10 -0.10	+0.15 -0.15	+0.05 -0.05




Reel [mm]



SPEC	16	24	32	44	56
DIM		✓			
A'' ± 0.5	16.5	24.5	32.5	44.5	56.5
B'' ± 0.3	2.10	2.10	2.10	2.10	2.10
C'' ± 0.5	100	100	100	100	100



CLASSIFICATION REFLOW PROFILE FOR SMT COMPONENTS



Profile Feature		Value
Preheat Temperature Min	$T_{s \text{ min}}$	150°C
Preheat Temperature Max	$T_{s \text{ max}}$	200°C
Preheat Time t_s from $T_{s \text{ min}}$ to $T_{s \text{ max}}$	t_s	100 seconds
Ramp-up Rate (T_L to T_p)		3°C/second max.
Liquidous Temperature	T_L	217°C
Time t_L maintained above T_L	t_L	60-150 seconds
Peak package body temperature	T_p	$T_p \leq T_c$, see Table below
Time within 5°C of actual peak temperature	t_p	30 seconds
Ramp-down Rate (T_p to T_L)		6°C/second max.
Time 25°C to peak temperature		5 minutes max.

Refer to IPC/JEDEC J-STD-020F

PACKAGE CLASSIFICATION REFLOW TEMPERATURE (T_p)

Properties	Volume mm ³ <350	Volume mm ³ 350-2000	Volume mm ³ >2000
PB-Free Assembly/Package Thickness < 1.6 mm	260 °C	260 °C	260 °C
PB-Free Assembly/Package Thickness 1.6 mm - 2.5 mm	260 °C	250 °C	245 °C
PB-Free Assembly/Package Thickness > 2.5 mm	250 °C	245 °C	245 °C

Refer to IPC/JEDEC J-STD-020F

ORDER INFORMATION

Order Code	Marking Code*	Weight (g/pcs)	Package Type	Quantity (pcs/Reel)
RMR-003-A55S-R	RMR-003	0.23g	Tape & Reel	1500pcs

*Marking Code

RMR003—— Product Code

The product information and specifications may be subject to changes even without prior written notice. The product has been designed for various applications; its suitability lies in the responsibility of each customer. The products are not authorized for use in safety-critical applications without RECOM's explicit written consent. A safety-critical application is an application where a failure may reasonably be expected to endanger or cause loss of life, inflict bodily harm or damage property. The applicant shall indemnify and hold harmless RECOM, its affiliated companies and its representatives against any damage claims in connection with the unauthorized use of RECOM products in such safety-critical applications.