Features

Unregulated Converters

- Fully RoHS 10/10 conform
- Full power at 100°C ambient temperature
- 1kVDC or 3kVDC isolation option
- Suitable for fully automated assembly (including vapor phase soldering)
- Optional continuous short circuit protection



R0.25S & R0.25D(A)

0.25 Watt SMD Single, Dual and Independent Outputs













UL60950-1 certified CAN/CSA-C22.2 No. 60950-1-07 certified IEC/EN60950-1 certified EN55032 compliant CB report



Description

The R0.25S and R0.25D(A) converters are of the enclosed open frame type, i.e. they are not potted. The converters are typically used in general purpose and industrial low power isolation and voltage matching applications where an SMD converter is required. The converter series feature an extended ambient temperature operating range of -40° C to $+100^{\circ}$ C without derating and optional continuous short circuit protection. In addition to single, dual and independent outputs, two isolation options and three different case formats, the converters are also available prepacked as tape and reel for use with automatic insertion machines.

Selection Guide				
Part Number	nom. Input Voltage [VDC]	Output Voltage [VDC]	Output Current [mA]	max. Capacitive Load ⁽²⁾ [µF]
R0.25S (3)-xx3.3 (4,5)	3.3, 5, 12, 15, 24	3.3	76	1000
R0.25S (3)-xx05 (4,5)	3.3, 5, 12, 15, 24	5	50	470
R0.25S (3)-xx09 (4,5)	3.3, 5, 12, 15, 24	9	28	470
R0.25S (3)-xx12 (4,5)	3.3, 5, 12, 15, 24	12	21	150
R0.25S (3)-xx15 (4,5)	3.3, 5, 12, 15, 24	15	17	68
R0.25S (3)-xx24 (4,5)	3.3, 5, 12, 15, 24	24	10.4	68
R0.25D (3)-xx3.3 (4,5)	3.3, 5, 12, 15, 24	±3.3	±38	470
R0.25D (3)-xx05 (4,5)	3.3, 5, 12, 15, 24	±5	±25	220
R0.25D (3)-xx09 (4,5)	3.3, 5, 12, 15, 24	±9	±14	68
R0.25D (3)-xx12 (4,5)	3.3, 5, 12, 15, 24	±12	±10.4	68
R0.25D (3)-xx15 (4,5)	3.3, 5, 12, 15, 24	±15	±8.3	68
R0.25D (3)-xx24 (4,5)	3.3, 5, 12, 15, 24	±24	±5.2	33
R0.25DA (3)-xx0505 (4,5)	3.3, 5, 12, 15, 24	5/5	25/25	220/220
R0.25DA (3)-xx1212 (4,5)	3.3, 5, 12, 15, 24	12/12	10/10	68/68

Notes:

Note1: Efficiency is tested at nominal input and full load at +25°C ambient

Note2: Max Cap Load is tested at nominal input and full resistive load and is defined as the capacitive load that will allow start up in under 1s without damage to the converter

Model Numbering



Notes:

Note3: R0.25S: without marking denotes 5 pins out of 8 fitted (includes /H option)

with marking "8" denotes 8 pins out of 8 fitted (/H option not available) with marking "12" denotes 10 pins out of 12 fitted (includes /H option)

R0.25D: without marking denotes "6" pins out of 10 fitted (includes /H option)

with marking "10" denotes 10 pins out of 10 fitted (/H option not available) with marking "12" denotes 10 pins out of 12 fitted (includes /H option)

R0.25DA: without marking denotes 7 pins out of 10 fitted (/H option not available)

Note4: standard part is without continuous short circuit protection

add suffix "/P" for continuous short circuit protection

add suffix "/H" for 3kVDC isolation (not available for R0.25S8, R0.25D10, R0.25DA) or add suffix "/HP" for 3kVDC isolation and continuous short circuit protection

Note5: add suffix "-R" for tape and reel packaging (compatible with all other suffixes)





Series

Specifications (measured @ Ta= 25°C, nom. Vin, full load and after warm-up unless otherwise stated)

BASIC CHARACTERISTICS				
Parameter	Condition	Min.	Тур.	Max.
Input Voltage Range			±10%	
Efficiency		60%		70%
Minimum Load		0%		
Internal Operating Frequency		20kHz	50kHz	90kHz
Output Ripple and Noise	20MHz BW			100mVp-p

Efficiency vs. Load






REGULATIONS			
Parameter	Con	dition	Value
Output Accuracy			±5.0% typ. / ±7.0% max.
Line Regulation	low line to high line, full load		2.0% max.
Load Regulation (6)	10% to 100% load	3.3Vout 5, 5/5Vout 9Vout 12, 12/12, 15, 24Vout	15.0% typ. / 20.0% max. 12.0% typ. / 15.0% max. 7.0% typ. / 10.0% max. 6.0% typ. / 10.0% max.

Notes:

Note6: Operation below 10% load will not harm the converter, but specifications may not be met


Tolerance Envelope





Series

Specifications (measured @ Ta= 25°C, nom. Vin, full load and after warm-up unless otherwise stated)



PROTECTIONS				
Parameter		Туре		
Short Circuit Protection (SCP)	below 100mΩ	below 100mΩ without suffix with suffix "/P"		1 second continuous
	I/P to O/P	without suffix	tested for 1 second rated for 1 minute	1kVDC 500VAC/60Hz
Isolation Voltage ⁽⁷⁾	I/P to 0/P	with suffix "/H"	tested for 1 second rated for 1 minute	3kVDC 1.5kVAC/60Hz
	0/P to 0/P	R0.25DA	tested for 1 second	1kVDC
Isolation Resistance		Viso=500V 10G		
Isolation Capacitance		75pF ma		
Insulation Grade		according to 60950-1 function		

Notes:

Note7: For repeat Hi-Pot testing, reduce the time and/or the test voltage


Note8: Refer to local safety regulations if input over-current protection is also required. Recommended fuse: slow blow type

ENVIRONMENTAL				
Parameter	Condition		Value	
Operating Temperature Range	full load @ free air convection, refer to "Der	ating Graph"	-40°C to +100°C	
Operating Altitude	according to 60950-1		2000m	
Operating Humidity	non-condensing	non-condensing 95% RH ma		
Pollution Degree			PD2	
MTBF	according to MIL LIDBY 217E C.B.	+25°C	4423 x 10 ³ hours	
MTBF according to MIL-HDBK-217F, G.B. +85°C +85°C		+85°C	2161 x 10 ³ hours	
	continued on next page			



Series


Specifications (measured @ Ta= 25°C, nom. Vin, full load and after warm-up unless otherwise stated)




SAFETY AND CERTIFICATIONS		
Certificate Type (Safety)	Report Number	Standard
Information Technology Equipment, General Requirements for Safety	E358085-A2-UL	UL60950-1, 2nd Edition:2007
information recliniology Equipment, denetal nequirements for Safety	L330003-A2-0L	CAN/CSA C22.2 No. 60950-1-07, 2nd Edition:2007
Information Technology Equipment, General Requirements for Safety	LVD1605077-08	IEC60950-1:2005, 2nd Edition + A2:2013
information recliniology Equipment, deneral nequirements for Safety	LVD1003077-00	EN60950-1:2006 + A2:2013
Information Technology Equipment, General Requirements for Safety (CB Scheme)	E322406-A2-CB-1	IEC60950-1:2001, 1st Edition
Medical Electrical Equipment Part 1: General Requirements for Basic Safety and	SPC1005061	IEC60601-1:1988 + A2:1995
Essential Performance	3501003001	EN 60601-1:1990 +A13:1996
EAC	RU-AT.49.09571	TP TC 004/2011
RoHS2		RoHS-2011/65/EU + AM-2015/863

EMC Compliance	Condition	Standard / Criterion
Electromagnetic compatibility of multimedia equipment - Emission requirements	with external filter (see filter suggestion below)	EN55032, Class B

EMC Filtering Suggestions according to EN55032 Class $\ensuremath{\mathsf{B}}$





Component List Class B

nom. Vin	C1	C2	L1
3.3VDC	2.2µF MLCC	470°E/414/DO	3.3µH SMD Inductor
5VDC	2.2μΓΙΝΙΔΟ		4.7µH SMD Inductor
12, 15VDC	1.0µF MLCC	470pF/4kVDC	2.2µH SMD Inductor
24VDC	470nF MLCC		47µH SMD Inductor



Series

Specifications (measured @ Ta= 25°C, nom. Vin, full load and after warm-up unless otherwise stated)

Component List Class B

nom. Vin	C1	C2	C3	L1
3.3VDC	2.2µF MLCC	470pF		3.3µH SMD Inductor
5VDC	Z.ZµF IVILOU			470pF
12, 15VDC	1.0µF MLCC	2kVDC	2kVDC	2.2µH SMD Inductor
24VDC	470nF MLCC			47µH SMD Inductor

DIMENSION AND PHYSICAL CHARACTERISTICS		
Parameter	Туре	Value
Material	case	non-conductive black plastic, (UL94 V-0)
Dimension (LxWxH)	R0.25S, R0.25S8	12.75 x 10.7 x 7.0mm
Difficion (Exwxn)	R0.25S12, R0.25D, R0.25D10, R0.25D12, R0.25DA	15.24 x 10.7 x 7.0mm
	R0.25S	1.0g typ.
Weight	R0.25S8	1.1g typ.
	R0.25S12, R0.25D, R0.25D10, R0.25D12, R0.25DA	1.2g typ.


Dimension Drawing (mm)

5 Pin Single SMD Package





/H option is available in this pin package



Pinning Information

Pin #	Single
1	-Vin
2	+Vin
4	-Vout
5	+Vout
8	NC

NC = No ConnectionTolerance: $xx.x = \pm 0.5mm$

 $xx.x = \pm 0.25$ mm



Series


Specifications (measured @ Ta= 25°C, nom. Vin, full load and after warm-up unless otherwise stated)


Dimension Drawing (mm)


6 Pin Dual SMD Package




/H option is available in this pin package









Recommended Footprint Details 10 **Top View** 1.20

Pinning Information

Pin #	Dual
1	-Vin
2	+Vin
4	Com
5	-Vout
7	+Vout
10	NC


NC = No Connection Tolerance:

 $xx.x = \pm 0.5$ mm

 $xx.xx = \pm 0.25mm$

8 Pin Single SMD Package

/H option is not available in this pin package



Pinning	Information

Pin #	Single
1	-Vin
2	+Vin
3	NC
4	-Vout
5	+Vout
6	NC
7	NC
8	NC

NC = No Connection Tolerance:

 $xx.x = \pm 0.5$ mm $xx.xx = \pm 0.25mm$




Series


Specifications (measured @ Ta= 25°C, nom. Vin, full load and after warm-up unless otherwise stated)


Dimension Drawing (mm)


10 Pin Dual SMD Package




/H option is not available in this pin package












Pinning Information


Pin#	Dual	R0.25DA
1	-Vin	-Vin
2	+Vin	+Vin
3	NC	no pin
4	Com	-Vout1
5	-Vout	+Vout1
6	NC	-Vout2
7	+Vout	+Vout2
8	NC	no pin
9	NC	no pin
10	NC	NC


NC = No Connection Tolerance: $xx.x = \pm 0.5$ mm $xx.xx = \pm 0.25$ mm


12 Pin Single and Dual SMD Package

/H option is available in this pin package









Recommended Footprint Details

00	7 12 11 10	- - 8	□; 7;	
2.0	Top Vi	ew	i	8
	1 2 3	5 - -	6 <u>;</u>	<u>ب</u>
1.20			3.8	

Pinning Information

Pin #	Single	Dual
1	-Vin	-Vin
2	+Vin	+Vin
3	NC	NC
5	-Vout	Com
6	NC	-Vout
7	NC	NC
8	+Vout	+Vout
10	NC	NC
11	NC	NC
12	NC	NC

NC = No Connection Tolerance: $xx.x = \pm 0.5mm$ $xx.xx = \pm 0.25mm$



Series

Specifications (measured @ Ta= 25°C, nom. Vin, full load and after warm-up unless otherwise stated)

PACKAGING INFORMATION			
Dealerging Dimension (LyMM)		tube	530.0 x 17.0 x 14.0mm
Packaging Dimension (LxWxH)		tape and reel (carton)	355.0 x 342.0 x 36.0mm
Packaging Quantity	tube	R0.25S, R0.25S8	40pcs
	tube	R0.25S12, R0.25D, R0.25D10, R0.25D12, R0.25DA	33pcs
		tape and reel	500pcs
Tape Width			24mm
Storage Temperature Range			-55°C to +125°C
Storage Humidity		non-condensing	95% RH max.

The product information and specifications may be subject to changes even without prior written notice. The product has been designed for various applications; its suitability lies in the responsibility of each customer. The products are not authorized for use in safety-critical applications without RECOM's explicit written consent. A safety-critical application is an application where a failure may reasonably be expected to endanger or cause loss of life, inflict bodily harm or damage property. The applicant shall indemnify and hold harmless RECOM, its affiliated companies and its representatives against any damage claims in connection with the unauthorized use of RECOM products in such safety-critical applications.

www.recom-power.com REV.: 2-2024 EC0-8