# **Features**

**Unregulated** 

**Converters** 

- 1:1 input range
- SMD package
- Efficiency up to 75%
- 1kVDC/1s isolation
- Wide operating
- Wide operating temperature range from -40°C to +85°C at full load
- UL/EAC certified


## Description

The R1SE series are 1W unregulated DC/DC converters that are lower cost than equivalent converters. The benefits of high volume production and semi-automatic assembly allow for a lower selling price without sacrificing our high quality standards. They are UL certified for safety, offer reasonable efficiency and operating temperature range of  $-40^{\circ}$  to  $+85^{\circ}$ C.



### R1SE

# 1 Watt SMD Single Output



#### Notes:

Note1: Efficiency is tested at nominal input and full load at +25°C ambient

Note2: Max Cap Load is tested at nominal input and full resistive load and is defined as the capacitive load that will allow start up in under 1s without damage to the converter











UL60950-1 certified CAN/CSA-C22.2 No. 60950-1-07 certified

#### **Model Numbering**



#### Notes:

Note3: without marking denotes 5 pins out of 8 fitted with marking "8" denotes 8 pins out of 8 fitted Note4: add suffix "-R" for tape and reel packaging

#### **Ordering Examples:**

R1SE-0505 = Single Output, 5 pins out of 8 fitted, 5Vin, 5Vout
R1SE-0505-R = Single Output, 5 pins out of 8 fitted, 5Vin, 5Vout Output and tape and reel packaging
R1SE8-0505 = Single Output, 8 pins out of 8 fitted, 5Vin, 5Vout




# **Series**

#### Specifications (measured @ Ta= 25°C, nom. Vin, full load and after warm-up unless otherwise stated)

BASIC CHARACTERISTICS				
Parameter	Condition	Min.	Тур.	Max.
Input Voltage Range			±10%	
Internal Operating Frequency		20kHz		70kHz
Output Ripple and Noise	20MHz BW		68mVp-p	100mVp-p

#### Efficiency vs. Load




REGULATIONS				
Parameter	Condition	Value		
Output Accuracy		-2.0% typ. / ±5.0% max.		
Line Regulation	low line to high line, full load	±1.2% typ.		
Load Regulation (5)	10% to 100% load	10.0% typ. / 15.0% max.		

#### Notes:

Note5: Operation below 10% load will not harm the converter, but specifications may not be met


#### **Tolerance Envelope**





## **Series**

#### Specifications (measured @ Ta= 25°C, nom. Vin, full load and after warm-up unless otherwise stated)



PROTECTIONS			
Parameter		Туре	Value
Short Circuit Protection (SCP)	belo	below 100mΩ	
Isolation Voltage (6)	I/P to O/P	tested for 1 second rated for 1 minute	1kVDC 500VAC/60Hz
Isolation Resistance	Vis	o = 500V	10G $Ω$ min.
Isolation Capacitance			75pF max.
Insulation Grade			functional

#### Notes:

Note6: For repeat Hi-Pot testing, reduce the time and/or the test voltage

Note7: Refer to local safety regulations if input over-current protection is also required. Recommended fuse: slow blow type

ENVIRONMENTAL				
Parameter	Condition		Value	
Operating Temperature Range	full load @ free air convection	ı	-40°C to +85°C	
Operating Altitude			2000m	
Operating Humidity	non-condensing	non-condensing 95% RH max		
Pollution Degree			PD2	
MTBF	according to MIL-HDBK-217F, G.B.	+25°C	1022 x 10 <sup>3</sup> hours	
INITER	according to Mil-HDBK-217F, G.B.	+85°C	172 x 10 <sup>3</sup> hours	
	continued on next page			




## **Series**

EN55032, Class A

#### **Specifications** (measured @ Ta= 25°C, nom. Vin, full load and after warm-up unless otherwise stated)






SAFETY AND CERTIFICATIONS		
Certificate Type (Safety)	Report / File Number	Standard
Information Technology Equipment, General Requirements for Safety	E358085-A2-UL	UL60950-1, 2nd Edition:2007
information reclinology Equipment, deficial nequirements for Safety	L0J000J-AZ-UL	CAN/CSA C22.2 No. 60950-1-03, 2nd Edition:2007
EAC	RU-AT.49.09571	TP TC 004/2011
RoHS 2+		RoHS-2011/65/EU + AM-2015/863
EMC Compliance	Condition	Standard / Criterion
Electromagnetic compatibility of multimedia equipment -	with external filter	EN55032, Class B

(see filter suggestion below)

#### **EMC Filter Suggestion according to EN55032**

Emission requirements



#### **Component List Class A**

MODEL	C1	L1	C2	C3 and C4
R1SE-0505	N/A	N/A	6.8µF 50V MLCC	N/A

#### **Component List Class B**

MODEL	C1	L1	C3 (safety)	C4 (safety)
R1SE-0505	10μF 100V MLCC	12µH choke RLS-126	330pF	330pF

#### Notes:

Note8: Filter suggestions are valid for indicated part numbers only. For other part numbers, please contact RECOM tech support for advice



## **Series**

#### Specifications (measured @ Ta= 25°C, nom. Vin, full load and after warm-up unless otherwise stated)


DIMENSION AND PHYSICAL CHARACTERISTICS				
Parameter	Туре	Value		
Material	case	non-conductive black plastic, (UL94 V-0)		
Dimension (LxWxH)		12.75 x 10.7 x 6.7mm		
Weight		1.0g typ.		


#### Dimension Drawing (mm)



10.7

# 5 Pin Single SMD Package





Pinning Information			
Pin #	Single		
1	-Vin		
2	+Vin		
4	-Vout		

+Vout

8 NC


NC = No Connection


Tolerance:


xx.xx= 0.25mm

5


#### 8 Pin Single SMD Package







0.5	00	-		
	1	2	3	4
	Bot	ton	n V	iew
	8	7	6	5
2.54				



Pin#	Single
1	-Vin
2	+Vin
4	-Vout
5	+Vout
3,6,7,8	NC

NC = No Connection Tolerance: xx.xx= 0.25mm

PACKAGING INFORMATION		
Packaging Dimension (LxWxH)	tube	530.0 x 17.0 x 14.0mm
T dordging Binonolon (EXVXII)	tape and reel (carton)	355.0 x 342.0 x 36.0mm
Packaging Quantity	tube	40pcs
Packaging Quantity	tape and reel	500pcs
Tape Width		24.0mm
Storage Temperature Range		-55°C to +125°C
Storage Humidity	non-condensing	95% RH max.

The product information and specifications may be subject to changes even without prior written notice. The product has been designed for various applications; its suitability lies in the responsibility of each customer. The products are not authorized for use in safety-critical applications without RECOM's explicit written consent. A safety-critical application is an application where a failure may reasonably be expected to endanger or cause loss of life, inflict bodily harm or damage property. The applicant shall indemnify and hold harmless RECOM, its affiliated companies and its representatives against any damage claims in connection with the unauthorized use of RECOM products in such safety-critical applications.