## **Features**

Regulated

**Converters** 

- 2:1 input voltage range
- Efficiency up to 81%
- EMI Class A without external components
- Continuous short circuit protection
- No minimum load required



## REC5A

## 5 Watt DIP24 Package













UL60950 certified UL62368 certified IEC/EN62368-1 certified

## Description

The REC5A series is cost efficient, general purpose isolated DC/DC converter containing a built in Class A EMC filter. The converter is designed to run from industry standard 24V or 5V unregulated supplies and is typically used to provide an isolated, regulated, short circuit protected output. Under Voltage Lockout is available as an option. These converters are designed for industrial applications, can drive high capacitive loads and operate over the full -40°C to +68°C temperature range without derating.

Selection Guide					
Part Number	Input Voltage Range [VDC]	Output Voltage [VDC]	Output Current [mA]	Efficiency typ. <sup>(1)</sup> [%]	max. Capacitive Load <sup>(2)</sup> [μF]
REC5A-0505SW/H2 <sup>(3)</sup>	4.5-9	5	1000	73.5	6800
REC5A-2405SW/H2 (3)	18-36	5	1000	81	6800

#### Notes:

Note1: Efficiency is test by nominal input and full load at  $+25^{\circ}$ C ambient Note2: Max Cap Load is test by nominal input and full resisitive load

## **Model Numbering**



#### **Ordering Examples:**

REC5A-0505SW/H2: Single Output, 4.5-9Vin (2:1) and 5Vout, 2kVDC Isolation REC5A-2405SW/H2/X1: Single Output, 18-36Vin (2:1) and 5Vout, 2kVDC Isolation, UVLO option

#### Notes:

Note3: without suffix is without Under Voltage Lockout Option add suffix "/X1" for optional Under Voltage Lockout

## Specifications (measured @ Ta= 25°C, nom. Vin and full load unless otherwise stated)


BASIC CHARACTERISTICS					
Parameter		Condition	Min.	Тур.	Max.
Internal Input Filter					Pi Type
Input Voltage Range	nom. Vin = 5V		4.5VDC		9VDC
input voltage hange	no	m. Vin = 24V	18VDC		36VDC
Input Surge Voltage		Vin = 5V			10VDC
Input Surge voltage		Vin = 24V			50VDC
Quiescent Current	Vin = 5V Vin = 24V			85mA	
Quiescent Guirent				16mA	
Start-up Time				10ms	
Internal Operating Frequency			120kHz		
Minimum Load			0%		
Output Ripple and Noise		vith 20MHz bandwidth 'µF ceramic capacitor			50mVp-p
	Vin =5V	DC-DC ON			3.2VDC
Under Voltage Leekeut (3)	VIII =5V	DC-DC OFF		3.0VDC	
Under Voltage Lockout (3)	Vin = 24V	DC-DC ON			16.5VDC
		DC-DC OFF		15.6VDC	
continued on next page					



# REC5A

# **Series**

## Specifications (measured @ Ta= 25°C, nom. Vin and full load unless otherwise stated)



Parameter	Conc	lition	Value
Output Accuracy	Oone	iidoii	±2.0% typ
Line Regulation	low line to	high line	±0.3% max
Load Regulation	0% to 10		0.6% max
Deviation vs. Load	0,000	70 70 1000	0.070
REC5A-0505S	SW/H2		REC5A-2405SW/H2
0.45	70.70.70.70.70.70.70.70.70.70.70.70.70.7	0.6	
0.4	7.7.7.7.7.7.	0.5	
0.35		0.0	
		0.4	
<u>\$</u> 0.25		<u> </u>	
in 0.2		0.3 <b>ati</b>	
0.25 0.25 0.25 0.15		Deviation [%]	
0.13	4.5Vin	0.2	18Vin
0.1	7Vin	0.1	24Vin -
0.05	9Vin		36Vin
0 10 20 30 40 50	0 60 70 80 90 100	0 10 20	30 40 50 60 70 80 90 100
0 10 20 30 40 50 Output L		0 10 20	Output Load [%]

PROTECTIONS			
Parameter		Condition	Value
Short Circuit Protection (SCP)		below 100mΩ	continuous, automatic recovery
Over Load Protection (OLP)			120% min., 140% typ.
Isolation Voltage <sup>(4)</sup>		tested for 1s	2kVDC
Isolation Resistance			1GΩ min.
Isolation Capacitance			2200pF max.
Insulation Grade			functional
	Notes:		
	Note4:	For repeat Hi-Pot testing, reduce the ime and/or the test	t voltage



# REC5A

## **Series**

## Specifications (measured @ Ta= 25°C, nom. Vin and full load unless otherwise stated)

Condition	Value
without derating with derating	-40°C to +68°C -40°C to +100°C
	+105°C
	±0.05%/°C
	20°C/W
	5000m
non-condensing	5% to 95% RF
	PD2
according to MIL-HDBK-217F, G.B. +25°C +68°C	1546 x 10³Ի 555 x 10³Ի
90 80 70 60 50 40 30 20 10 -40 -30 -20 -10 0 10 20 30 40 50 60 .70 80 90 100 110	
	with derating with derating  non-condensing  according to MIL-HDBK-217F, G.B.  +25°C +68°C  100 90 80 70 60 50 40 30 20 10 -40 -30 -20 -10 0 10 20 30 40 50 60 /70 80 90 100 110

Certificate Type	Report / File Number	Standar
Information Technology Equipment, General Requirements for Safety	E224736	UL60950-1, 2nd Edition, 201 CSA C22.2 No. 60950-1, 2nd Edition, 201
Audio/Video, information and communication technology equipment	E224736	UL62368-1, 2nd Edition, 201 CSA C22.2 No. 62368-1, 201
Audio/video, information and communication technology equipment. Safety requirements (CB Scheme)	L0339m35-CB-1-B1	IEC62368, 2nd Edition, 201 EN62368, 1st Edition, 201
EAC	RU-AT.49.09571	TP TC 004/201
RoHs 2		RoHS 10/10, 2011/65/EU + AM-2015/86
EMC Compliance	Condition	Standard / Criterio
Information technology equipment - Radio disturbance characteristics - Limits and methods of measurement <sup>(5)</sup>	with external components	EN55032, Class
ESD Electrostatic discharge immunity test	Air ±8kV and Contact ±4kV	EN61000-4-2, Criteria
Radiated, radio-frequency, electromagnetic field immunity test	3 V/m	EN61000-4-3, Criteria
Fast Transient and Burst Immunity	±0.5kV	EN61000-4-4, Criteria
Surge Immunity	±0.5kV	EN61000-4-5, Criteria
Immunity to conducted disturbances, induced by radio-frequency fields	3 Vr.m.s	EN61000-4-6, Criteria
Power Magnetic Field Immunity	50Hz, 1A/m	EN61000-4-8, Criteria



# REC5A

## **Series**

## Specifications (measured @ Ta= 25°C, nom. Vin and full load unless otherwise stated)


# EMC Filtering Suggestions according to EN55032 +V<sub>IN</sub> OC1 C2 C2 C2 C-V<sub>OUT</sub>


## **Component List Class B**

MODEL	C1	C2	C3
REC5A-0505SW/H2	47μF/50V	47μF/50V	N/A
REC5A-2405SW/H2	47μF100V	47μF/100V	1000pF/3kV

DIMENSION and PHYSICAL CHARACTERISTICS				
Parameter	Туре	Value		
	case	non-conductive black plastic (UL94V-0)		
Material	base	non-conductive black plastic (UL94V-0)		
	potting	epoxy (UL94V-0)		
Dimension (LxWxH)		31.8 x 20.3 x 10.2mm		
Weight		13.0g		

## **Dimension Drawing (mm)**









#### **Pin Connections**

Pin #	Function		
2, 3	-Vin		
9	NC		
11	NC		
14	+Vout		
16	-Vout		
22, 23	+Vin		

Tolerance: X.X ±0.5mm X.XX ±0.25mm

PACKAGING INFORMATION				
Packaging Dimension (LxWxH)	Tube	520 x 22.7 x 18.3mm		
Packaging Quantity		15pcs		
Storage Temperature Range		-55°C to +125°C		

The product information and specifications may be subject to changes even without prior written notice. The product has been designed for various applications; its suitability lies in the responsibility of each customer. The products are not authorized for use in safety-critical applications without RECOM's explicit written consent. A safety-critical application is an application where a failure may reasonably be expected to endanger or cause loss of life, inflict bodily harm or damage property. The applicant shall indemnify and hold harmless RECOM, its affiliated companies and its representatives against any damage claims in connection with the unauthorized use of RECOM products in such safety-critical applications.