Features TRIAC Dimmable LED **Driver**

- Triac –dimmable with leading or trailing edge dimmers
- Class II with SELV output (no earth required)
- Extra-large screw terminals and integrated cable clamps for easy installation
- Power factor corrected >0.95 • Dimming range 1..100%
- Compatible with a wide range of dimmers

Description

The RACT09-xxx series are low cost, triac-dimmable, constant current 9W LED drivers available with either 350mA, 500mA or 700mA full-range outputs. The drivers are Class II (double insulated) meaning no earth connection is required. The phase angle dimming works with leading or trailing edge dimmers. The RACT09 is suitable for indoor locations up to 50°C ambient temperature and is certified for building into furniture for applications such as dimmable shelf lighting, cove lighting or accent lighting. It is CE marked (LVD + EMC + RoHS), EAC and has IEC61347-1/IEC61347-2-13 CB report certification.

Selection Guide					
Part Number	Input Voltage Range [VAC]	Output Voltage Range [VDC]	Output Current [mA]	Efficiency min. @rated loa [%]	Output d Power [W]
RACT09-350	198-264	13-26	350	80	9
RACT09-500	198-264	9-18	500	81	9
RACT09-700	198-264	7-13	700	76	9

All LED Drivers may not be used without a load. They must be switched on the primary side only. Noncompliance may damage the LED or reduce its lifetime.

Specifications (measured @ Ta= 25°C, 240VAC, rated load unless otherwise specified)

RACT09-

BASIC CHARACTERISTICS						
Parameter	Condition	Min.	Тур.	Max.		
Input Voltage Range		198VAC	230VAC	264VAC		
Input Current				60mA		
Inrush Current	full load			5A		
No Load Power Consumption				1W		
Input Frequency Range		50Hz		60Hz		
Power Factor	full load	0.95				
	continued on next	page				



RACT09

9 Watt

TRIAC

Dimmable **Single Output**



IEC/EN61347 certified IEC/EN61347-2-13 certified EN61547 certified EN62493 certifed EN55015 compliant **CB** report

Model Numbering

Output Power ·

Output Current

RECOM AC/DC Converter

RACT09 Series

Specifications (measured @ ta= 25°C, 240VAC, rated load unless otherwise specified)

Parameter	Condition	Min.	Тур.	Max.
THD	full load			25%
Start-up Time				500ms
Internal Operating Frequency			60kHz	
	RACT09-350			175mA
Output Ripple Current (1)	RACT09-500			350mA
	RACT09-700			900mA

Note1: Measured at 20MHz BW by using a 12" twisted pair-wie terminated with a 0.1µF and 47µF capacitor parallel across output

REGULATIONS		
Parameter	Condition	Value
Output Accuracy		±5% typ.
Load Regulation		5% max.
Line Regulation		5% max.

PROTECTION				
Parameter	Co	ondition		Value
Input Fuse				fusible resistor
Short Circuit Protection (SCP)			Latch OFF, auto	recovery after fault condition is removed
Over Voltage Protection (OVP)	RAC	CT09-350 CT09-500 CT09-700	31VDC max. 25VDC max. 17VDC max.	Latch OFF, auto recovery after fault condition is removed
Over Load Protection (OLP)			Latch OFF, aut	o recovery after fault condition is removed
Over Temperature Protection (OTP)		110°C	Latch OFF, aut	o recovery after fault condition is removed
Isolation Voltage	I/P to O/P	tested for 1 minute		3.75kVAC
Leakage Current				5mA max.
Movimum loading of outomotic oir				

Maximum loading of automatic circuit breakers*


* @ 230VAC, 10hm,	90°	phase	angle	and	max.	load
-------------------	-----	-------	-------	-----	------	------

Circuit Breaker	Circuit Breaker Current				
Тур	10A	16A	20A	25A	
В	36	57	69	85	
С	57	87	109	134	

ENVIRONMENTAL		
Parameter	Condition	Value
Operating Temperature Range	without derating @ natural convection 0.1m/s (see graph)	-20°C to +50°C
Max. Case Temperature	at tc point	+80°C max.
Operating Humidity	non-condensing	5-85% RH
IP Rating		IP20
Pollution Degree		PD2
Design Lifetime	+25°C ambient	>30 x 10 ³ hours

continued on next page

Specifications (measured @ Ta= 25°C, 240VAC, rated load unless otherwise specified)



Certificate Type (Safety)	Report Number	Standard
Lamp controlgear Part 1: General and safety requirements (CB Scheme)	325797	IEC61347-1:2007 2nd Edition + A2:2012
	323797	IEC01347-1:2007 2110 EUILIOIT + A2:2012
Lamp controlgear Part 2-13: Particular requirements for d.c. or a.c. supplied electronic controlgear for LED modules (CB Scheme)	325797	IEC61347-2-13:2014 2nd Edition
Lamp controlgear Part 1: General and safety requirements (LVD)		EN61347-1:2015
Lamp controlgear Part 2-13: Particular requirements for d.c. or a.c. supplied electronic controlgear for LED modules (LVD)		EN61347-2-13:2014 + A1:2017
Lamp controlgear Part 1: General and safety requirements	325797	EN61347-1:2008 + A2:2013
Lamp controlgear Part 2-13: Particular requirements for d.c. or a.c. supplied electronic controlgear for LED modules	325797	EN61347-2-13:2014
EAC	RU-AT.49.09571	TP TC 004/2011
RoHS 2+		RoHS 2011/65/EU + AM2015/863
EMC Compliance	Condition	Standard / Criterion
Limits and methods of measurement of radio disturbance characteristics of electrical		EN55015:2013 + A1:2015
lighting and similar equipment	305985	
Equipment for general lighting purposes – EMC immunity requirements Assessment of lighting equipment related to human exposure to electromagnetic fields		EN61547:2009
		EN62493:2015
ESD Electrostatic discharge immunity test	Air ±8kV, Contact ±4kV	EN61000-4-2:2009, Criteria A
Radiated, radio-frequency, electromagnetic field immunity test	3V/m	EN61000-4-3:2006 + A2:2010, Criteria A
Fast Transient and Burst Immunity	AC Power Port: ±1kV DC Power Port: ±0.5kV	EN61000-4-4:2012, Criteria A
Surge Immunity	AC Power Port: ±0.5kV	EN61000-4-5:2014, Criteria A
Immunity to conducted disturbances, induced by radio-frequency fields	3V/m	EN61000-4-6:2014, Criteria A
Voltage Dips and Interruptions	Voltage Dips >95%	EN61000-4-11:2004, Criteria B
Voltage Dips and Interruptions	Voltage Dips 30%	EN61000-4-11:2004, Criteria B
Limits of Harmonic Current Emissions		EN61000-3-2:2014, Class C
	-	EN61000-3-3:2013, Clause 5

RECOM **AC/DC** Converter

RACT09 Series

DIMENSION and PHYSICAL CHARACTERI	STICS				
Parameter	Туре				Valu
	case		plastic (UL94)		
Vaterial	PCB				FR4 (UL94V-0
Package Dimension (LxWxH)				109.0 x 4	10.0 x 22.0mr
Package Weight					70g typ
Dimensions Drawing (mm)					
▲ 109.0					
PR	- sec	rec tc= FC	re stripping length: commended tighter = case temperature = fixing centers erance: xx.x= : xx.xx= :	ing torque: 0.25Nm measuring point ±1.0mm	
	22.0				
Bottom View	0.00 tc 39.0	Connection v	via Screw Ter Solid Wire	minal Stranded Wire ⁽²⁾	AWG
			0.75-2.5mm ²	0.75-2.5mm ²	20-14
			0.75-2.5mm ²	0.75-2.5mm ²	20-14
FC 13.3		LED+	0.5-2.5mm ²	0.5-2.5mm ²	21-14

without cable cover's 27.5 66.1 15.4 0.0 15.0 **Top View** <u>R1.7</u> Ν SEC PR

Notes:

LED-

Note2: The use of sleeve or ferrule terminations is recommended

0.5-2.5mm²

21-14


0.5-2.5mm²

6.4

RECOM AC/DC Converter

RACT09 Series

Specifications (measured @ Ta= 25°C, 240VAC, rated load unless otherwise specified)



PACKAGING INFORMATION				
Parameter	Туре	Value		
Packaging Dimension (LxWxH)	cardboard box	270.0 x 127.0 x 48.0mm		
Packaging Quantity		10pcs		
Storage Temperature Range		-20°C to +70°C		
Storage Humidity	non-condensing	5-85% RH		

The product information and specifications may be subject to changes even without prior written notice. The product has been designed for various applications; its suitability lies in the responsibility of each customer. The products are not authorized for use in safety-critical applications without RECOM's explicit written consent. A safety-critical application is an application where a failure may reasonably be expected to endanger or cause loss of life, inflict bodily harm or damage property. The applicant shall indemnify and hold harmless RECOM, its affiliated companies and its representatives against any damage claims in connection with the unauthorized use of RECOM products in such safety-critical applications.