Features

Switching Regulator

Description

automotive markets.

- Efficiency up to 94%, no need for heatsinks
- High reflow temperature SMD package
- Adjustable output voltage buck converter
- Short circuit protection, thermal shutdown
- Remote on/off control
- Very low shutdown current

RECON DC/DC Converter

R-78AA-1.0

1.0 Amp SMD Single Output

The R-78AAxx-1.0SMD series are adjustable output non-isolated buck converters that meet the requirements for RoHS 10/10 as well as the reflow soldering temperatures associated with vapor phase soldering, making these high efficiency switching regulators ideally suited to modern pick-and-place mass production. The efficiency of up to 97% means that very little energy

Selection Guide Part Input Output Vout Output Efficiency @ min Vin Voltage Range Number Voltage **Adjust Range** Current @ max. Vin [VDC] [VDC] [VDC] [A] [%] [%] R-78AA1.5-1.0SMD 4.75 - 18 1.5 fixed 1.0 77 73 R-78AA1.8-1.0SMD 4.75 - 18 1.8 1.5 - 3.0 1.0 82 76 R-78AA2.5-1.0SMD 4.75 - 18 2.5 1.5 - 3.0 1.0 87 81 R-78AA3.3-1.0SMD 4.75 - 18 3.3 3.0 - 5.51.0 90 84 R-78AA5.0-1.0SMD 6.5 - 18 5.0 3.0 - 5.5 1.0 89 94

is wasted as heat. The additional features of remote on/off control, continuous short circuit protection and adjustable output voltages will find many uses in the battery-powered, industrial, medical and



Note1: Input voltage ranges valid for nominal output voltages Vin must be higher than Vout including adjust range and dropout voltage










EN60950-1 certified IEC60950-1 certified

Model Numbering



Notes:

Note2: add suffix -R for tape & reel packaging

Ordering Examples:

R-78AA5.0-1.0SMD-R = 5.0VDC Output Volage, 1.0A, SMD, tape and reel packaging R-78AA2.5-1.0SMD = 2.5VDC Output Volage, 1.0A, SMD, tube



Series

Specifications (measured @ Ta= 25°C, 10% minimum load, unless otherwise stated)

BASIC CHARACTERISTICS				
Parameter	Condition	Min.	Тур.	Max.
Quiescent Current	Vin= min. to max.		5mA	7mA
Internal Power Dissipation				0.4W
Output Voltage Adjustability				see calculation
Minimum Load (2)		0%		
Start-up time	ON/OFF CTRL		50ms	
ON/OFF CTRL	DC-DC ON DC-DC OFF	Open or 2.8VDC <vr<5vdc GND or 0VDC<vr<0.8vdc< td=""></vr<0.8vdc<></vr<5vdc 		
Input Current of CTRL Pin	DC-DC OFF		1.8µA	
Standby Current			20μΑ	35μΑ
CTRL Thereshold Voltage		2.4VDC	2.6VDC	2.8VDC
CTRL Voltage Hysterese			250mV	
Internal Operating Frequency		335kHz	385kHz	435kHz
Output Ripple and Noise	20MHz BW		20mVp-p	30mVp-p
	with normal start-up time, no external components			470µF
Maximum Capacitive Load	with <1 second start-up time + diode protection circuit			6800µF

Notes:

Note3: Operation under no load will not harm the converter, but specifications may not be met.


A minimum load of 10mA is recommended


Output Voltage Adjustability Adjustment Resistor Values


	K1	K2	R3	Vref(V)
1.8V	10ΚΩ	21ΚΩ	5.6K Ω	1.23
2.5V	22ΚΩ	21ΚΩ	5.6K Ω	1.23
3.3V	16.9K Ω	10ΚΩ	5.6K Ω	1.23
5.0V	30.9K Ω	10ΚΩ	10ΚΩ	1.23

Trim down Rdown = $\frac{R2(R1 + R3) \times (Vref - Vo) + Vref \times R1R3}{R2Vo - Vref (R1 + R2)}$

Trim up
$$Rup = \frac{R2R3 \text{ (Vref - Vo)} + Vref R1 \text{ (R2 + R3)}}{R2 \text{ (Vo - Vref)} - Vref R1}$$










Series

Specifications (measured @ Ta= 25°C, 10% minimum load, unless otherwise stated)



REGULATIONS			
Parameter	Cond	dition	Value
Output Accuracy	full load		±2.0% typ. / ±3.0% max.
Line Regulation	low line to high line, full load		±0.2% typ. / ±0.4% max.
Load Regulation	10% to 100% load		±0.7% typ. / ±1.0% max.
Transient Response	25mA/μs	100% <-> 50% load	±85mV typ. / ±100mV max.



Series

Specifications (measured @ Ta= 25°C, 10% minimum load, unless otherwise stated)


PROTECTIONS		
Parameter	Condition	Value
Short Circuit Protection (SCP)		continuous, automatic recovery
Short Circuit Input Current	nom. Vin= 12VDC	120mA max.

Optional Diode Protection Circuit


Add a blocking diode to Vout if current can flow backwards into the output, as this can damage the converter when it is powered down.

The diode can either be fitted across the device if the source is low impedance or fitted in series with the output (recommended).

Optional Protection 1:




Optional Protection 2:



ENVIRONMENTAL			
Parameter	Condition		Value
Operating Temperature Range	with derating (see grap	oh)	-40°C to +85°C
Maximum Case Temperature			+100°C
Temperature Coefficient			±0.015%/°C
Thermal Impedance	0.1m/s, horizontal	0.1m/s, horizontal	
Operating Altitude			
Operating Humidity	non-condensing	non-condensing	
Pollution Degree			PD2
MTBF	according to MIL-HDBK-217F, G.B.	+25°C	13338 - 21070 x 10 ³ hours
INTE	according to MIL HDDIX 2171, d.D.	+ 71°C	3880 - 6769 x 10 ³ hours

Derating Graph






Series


Specifications (measured @ Ta= 25°C, 10% minimum load, unless otherwise stated)


SAFETY AND CERTIFICATIONS			
Certificate Type (Safety)	Report / File Number	Standard	
Information Technology Equipment, General Requirements for Safety	1603123	IEC60950-1:2005, 2nd Edition + AM 2:2013 EN60950-1:2006 + AM 2:2013	
EAC	RU-AT.49.09571	TP TC 004/2011 TP TC 004/2011	
RoHS 2+		RoHS 2011/65/EU + AM2015/863	
EMC Compliance	Condition	Standard / Criterion	
Electromagnetic compatibility of multimedia equipment - Emission requirements	with external filter	EN55032, Class B	
ESD Electrostatic discharge immunity test	Air ±8kV; Contact ±4kV	EN61000-4-2	
Radiated, radio-frequency, electromagnetic field immunity test	3V/m	EN61000-4-3	


DIMENSION AND PHYSICAL CHARACTERISTICS		
Parameter	Туре	Value
Material	case PCB	non-conductive black plastic, (UL94 V-2) FR4, (UL94 V-1)
Dimension (LxWxH)		15.3 x 9.6 x 8.8mm
Weight		1.7g typ.


Dimension Drawing (mm)











Pinning information

Pin #	Single
1,2	+Vin
3,7,8,9	GND
4,5	+Vout
6	Vadj
10	CTRL

Tolerance: xx.x = 0.5mm $xx.xx = \pm 0.25mm$



Series

Specifications (measured @ Ta= 25°C, 10% minimum load, unless otherwise stated)

PACKAGING INFORMATION		
Parameter	Туре	Value
Deckaging Dimension (LyM)/d D	tube	530.0 x 17.0 x 13.0mm
Packaging Dimension (LxWxH)	tape and reel (carton)	355.0 x 342.0 x 36.0mm
Packaging Quantity	tube	33pcs
	tape and reel	250pcs
Tape Width		24mm
Storage Temperature Range		-55°C to +125°C
Storage Humidity		95% RH max.

The product information and specifications may be subject to changes even without prior written notice. The product has been designed for various applications; its suitability lies in the responsibility of each customer. The products are not authorized for use in safety-critical applications without RECOM's explicit written consent. A safety-critical application is an application where a failure may reasonably be expected to endanger or cause loss of life, inflict bodily harm or damage property. The applicant shall indemnify and hold harmless RECOM, its affiliated companies and its representatives against any damage claims in connection with the unauthorized use of RECOM products in such safety-critical applications.

www.recom-power.com REV.: 5/2019 I-6