Features
TRIAC Dimmable
LED
Driver

- Triac –dimmable with leading or trailing edge dimmers
- Class II with SELV output (no earth required)
- Extra-large screw terminals and integrated cable clamps for easy installation
- Power factor corrected >0.95
- Dimming range 1..100%
 - Compatible with a wide range of dimmers

Description

The RACT25-xxx series are low cost, triac-dimmable, constant current 25W LED drivers available with either 500mA, 700mA or 1.05A full-range outputs. The drivers are Class II (double insulated) meaning no earth connection is required. The phase angle dimming works with leading or trailing edge dimmers. The RACT25 is suitable for indoor locations up to 50°C ambient temperature and is certified for building into furniture for applications such as dimmable shelf lighting, cove lighting or accent lighting. It is CE (LVD + EMC + RoHS) + EAC marked and has IEC61347-1/IEC61347-2-13 CB report certification.

RE	С		Μ
AC/DC	Co	onve	erter

RACT25

25 Watt

TRIAC



Dimmable Single Output

Selection Guide					
Part Number	Input Voltage Range [VAC]	Output Voltage Range [VDC]	Output Current [mA]	Efficiency min. @rated loa [%]	Output d Power [W]
RACT25-500	198-264	25-50	500	85	25
RACT25-700	198-264	18-36	700	85	25
RACT25-1050	198-264	12-24	1050	84	25

All LED Drivers may not be used without a load. They must be switched on the primary side only. Noncompliance may damage the LED or reduce its lifetime.



IEC/EN61347 certified IEC/EN61347-2-13 certified EN61547 certified EN62493 certified EN55015 compliant CB report

Model Numbering



Specifications (measured @ Ta= 25°C, 240VAC, rated load unless otherwise specified)				
BASIC CHARACTERISTICS				
Parameter	Condition	Min.	Тур.	Max.
Input Voltage Range		198VAC	230VAC	264VAC
Input Current				160mA
Inrush Current	full load			5A
No Load Power Consumption				1W
Input Frequency Range		50Hz		60Hz
Power Factor	full load	0.95		
continued on next page				

RECOM AC/DC Converter

RACT25 Series

Specifications (measured @ Ta= 25°C, 240VAC, rated load unless otherwise specified)

Parameter	Condition	Min.	Тур.	Max.
THD	full load			20%
Start-up Time				500ms
Internal Operating Frequency	RACT25-500		77kHz	
Internal Operating Frequency	RACT25-700, 1050		65kHz	
	RACT25-500			170mA
Output Ripple Current (1)	RACT25-700			260mA
	RACT25-1050			440mA
Notes:				

Note1: Measured at 20MHz BW by using a 12" twisted pair-wie terminated with a 0.1µF and 47µF capacitor parallel across output

REGULATIONS			
Parameter	Condition	Value	
Output Accuracy		±5% typ.	
Load Regulation		5% max.	
Line Regulation		5% max.	

PROTECTION					
Parameter	Co	ndition			Value
Input Fuse					fusible resistor
Short Circuit Protection (SCP)			Latch OF	F, auto reco	overy after fault condition is removed
Over Voltage Protection (OVP)	RAC RAC RAC	T25-500 T25-700 T25-1050	5 4 3	8VDC max. 5VDC max. 2VDC max.	Latch OFF, auto recovery after fault condition is removed
Over Load Protection (OLP)			Latch OF	F, auto reco	overy after fault condition is removed
Over Temperature Protection (OTP)	-	10°C	Latch OF	F, auto reco	overy after fault condition is removed
Isolation Voltage	I/P to O/P	tested for 1 minute			3.75kVAC
Leakage Current					5mA max.
Maximum loading of automatic circuit breakers*					
	* @ 230VAC,	10hm, 90° phase ai	ngle and max. load		
	Circuit Breake	r Circuit Br	eaker Current		

Circuit Breaker	Circuit Breaker Current			
Тур	10A	16A	20A	25A
В	24	38	46	58
С	38	62	74	92

ENVIRONMENTAL		
Parameter	Condition	Value
Operating Temperature Range	without derating @ natural convection 0.1m/s (see graph)	-20°C to +50°C
Max. Case Temperature	at tc point	+80°C max.
Operating Humidity	non-condensing	5-85% RH
IP Rating		IP20
Pollution Degree		PD2
Design Lifetime	+25°C ambient	>30 x 10 ³ hours

continued on next page

Specifications (measured @ Ta= 25°C, 240VAC, rated load unless otherwise specified)



SAFETY AND CERTIFICATIONS			
Certificate Type (Safety)	Report Number	Standard	
Lamp controlgear Part 1: General and safety requirements (CB Scheme)	325797	IEC61347-1:2007 2nd Edition + A2:2012	
Lamp controlgear Part 2-13: Particular requirements for d.c. or a.c. supplied electronic controlgear for LED modules (CB Scheme)	325797	IEC61347-2-13:2014 2nd Edition	
Lamp controlgear Part 1: General and safety requirements (LVD)		EN61347-1:2015	
Lamp controlgear Part 2-13: Particular requirements for d.c. or a.c. supplied electronic controlgear for LED modules (LVD)		EN61347-2-13:2014 + A1:2017	
Lamp controlgear Part 1: General and safety requirements	325797	EN61347-1:2008 + A2:2013	
Lamp controlgear Part 2-13: Particular requirements for d.c. or a.c. supplied electronic controlgear for LED modules	325797	EN61347-2-13:2014	
EAC	RU-AT.49.09571	TP TC 004/2011	
RoHS 2+		RoHS 2011/65/EU + AM2015/863	
EMC Compliance	Condition	Standard / Criterion	
Limits and methods of measurement of radio disturbance characteristics of electrical lighting and similar equipment		EN55015:2013 + A1:2015	
Equipment for general lighting purposes – EMC immunity requirements	305985	EN61547:2009	
Assessment of lighting equipment related to human exposure to electromagnetic fields		EN62493:2015	
ESD Electrostatic discharge immunity test	Air ±8kV, Contact ±4kV	EN61000-4-2:2009, Criteria A	
Radiated, radio-frequency, electromagnetic field immunity test	3V/m	EN61000-4-3:2006 + A2:2010, Criteria A	
Fast Transient and Burst Immunity	AC Power Port: ±1kV DC Power Port: ±0.5kV	EN61000-4-4:2012, Criteria A	
Surge Immunity	AC Power Port: ±0.5kV	EN61000-4-5:2014, Criteria A	
Immunity to conducted disturbances, induced by radio-frequency fields	3V/m	EN61000-4-6:2014, Criteria A	
	Voltage Ding >05%	EN61000-4-11:2004. Criteria B	
Voltage Dips and Interruptions	Voltage Dips >3570		
Voltage Dips and Interruptions Voltage Dips and Interruptions	Voltage Dips 30%	EN61000-4-11:2004, Criteria B	
Voltage Dips and Interruptions Voltage Dips and Interruptions Limits of Harmonic Current Emissions	Voltage Dips 30%	EN61000-4-11:2004, Criteria B EN61000-3-2:2014, Class C	

RECOM **AC/DC** Converter

RACT25 **Series**

Specifications (measured @ Ta= 25°C, 240VAC, I	rated load unless otherwise specified)	
DIMENSION and PHYSICAL CHARACTERIS	STICS	
Parameter	Туре	Value
Material	case	plastic (UL94V-2)
	РСВ	FR4 (UL94V-0)
Package Dimension (LXWXH)		120.0 X 45.0 X 28.0mm
		100g týp.
Dimensions Drawing (mm)		
120	0	
	<u> </u>	
		wire strinning length: 6-7mm
	+	recommended tightening torque: 0.25Nm
	SEC.	tc= case temperature measuring point FC= fixing centers
		Tolerance: $xx.x = \pm 1.0mm$
Bottom View		
		via Screw Terminal
		Solid Wire Stranded Wire ⁽²⁾ AWG
FC 13.3	VAC in (N) ().75-2.5mm ² 0.75-2.5mm ² 20-14
without cable cove	er`s <u>VAC in (L) (</u>	$0.75 - 2.5 \text{mm}^2$ $0.75 - 2.5 \text{mm}^2$ $20 - 14$
18.3 7	77.1 14.6 LED-	0.5-2.5mm ² 0.5-2.5mm ² 21-14
	Notes:	of sleeve or ferrule terminations is recommended
	V	

RECOM **AC/DC** Converter

RACT25 **Series**

Value

Specifications (measured @ Ta= 25°C, 240VAC, rated load unless otherwise specified)



PACKAGING INFORMATION			
Parameter	Туре	Value	
Packaging Dimension (LxWxH)	cardboard box	330.0 x 137.0 x 55.0mm	
Packaging Quantity		10pcs	
Storage Temperature Range		-20°C to +70°C	
Storage Humidity	non-condensing	5-85% RH	

The product information and specifications may be subject to changes even without prior written notice. The product has been designed for various applications; its suitability lies in the responsibility of each customer. The products are not authorized for use in safety-critical applications without RECOM's explicit written consent. A safety-critical application is an application where a failure may reasonably be expected to endanger or cause loss of life, inflict bodily harm or damage property. The applicant shall indemnify and hold harmless RECOM, its affiliated companies and its representatives against any damage claims in connection with the unauthorized use of RECOM products in such safety-critical applications.