
FEATURES



- JEDEC-reflow solder-able construction
- Full load line-rating from 85 to 265Vac
- -40°C to +80°C rated operating temperature
- 6000m operating altitude
- Shock and vibration stabilized
- No external components for floating loads
- 3 year warranty



Dimensions (LxWxH): 27.7 x 23.7 x 19.0mm (1.1 x 0.9 x 0.8 inch) 15.5g (0.034 lbs)



DESCRIPTION


The compact 3 Watt AC/DC power supplies series RAC03-K/SMT boast an optimized design tailored for JEDEC-reflow solder processes. With a mere $1in^2$ footprint, these units facilitate automated production, ensuring a shock and vibration-resistant PCBA. The fully integrated modules eliminate the need for external components in floating load configurations, providing safety-rated performance at altitudes up to 6000m. Operating seamlessly in temperatures ranging from -40 to +80°C, and offering a continuous 3-Watt output power from -25 to +60°C, these power supplies are engineered for reliability. Compliant with international standards, including EN/IEC/UL62368, EN60335, and IEC61558, they are an ideal solution for a diverse range of applications from IoT to industrial automation, driving sensors, household and monitoring devices, as well as housekeeping auxiliary power supplies, these power units are well-suited for domestic use.

Input Voltage Range [VAC]	Output Voltage nom. [VDC]	Output Current max. [mA]	Efficiency ⁽¹⁾ typ. [%]
85-265	3.3	900	69
85-265	5	600	74
85-265	12	250	78
85-265	15	200	75
85-265	18	170	78
85-265	24	125	77
	Range [VAC] 85-265 85-265 85-265 85-265 85-265 85-265 85-265 85-265	Range [VAC]nom. [VDC]85-2653.385-265585-2651285-2651585-26518	Range [VAC]nom. [VDC]max. [mA]1000

Note1: Efficiency is tested at nominal input (230VAC) and constant resistive load at +25°C ambient



MODEL NUMBERING




—— Tape and Reel Packaging —— Surface Mount Technology


Parameter		Cond	ition	Min.	Тур.	Max.
Nominal Input Voltage	50/60Hz		100VAC		240VAC	
Operating Dange (2)		47-6	3Hz	85VAC		265VAC
Operating Range ⁽²⁾		D	0	120VDC		370VDC
laput Current	115VAC		/AC			80mA
Input Current		230	/AC			40mA
law sh Ourrent			115VAC			10A
Inrush Current	cold start at	[25°	230VAC			20A
No Load Power Consumption	230VAC			100mW		
			0.3W			0.17W
Ecodesign Standby Mode Use (Available output power for stated input power)	Input Power=	0.5W			0.3W	
(Available output power for stated liput power)	1W		1W			0.7W
Input Frequency Range	AC Input		47Hz		63Hz	
Minimum Load			0%			
Power Factor	115VAC		0.5			
	230VAC		0.4			
Start-up time				20ms		
Rise time					15ms	
	115VAC			15ms		
Hold-up time	230VAC			80ms		
Internal Operating Frequency	100% load at nominal Vin				130kHz	
	RAC03-3.3SK/SMT; RAC03-05SK/SMT				80mVp-p	
Output Ripple and Noise (3)	20MHz BW all others				1% of nom \	

Note2: The products were submitted for safety files at AC-Input operation.

Note3: Measurements are made with a 0.1µF MLCC & 10µF E-cap in parallel across output. (low ESR)

RAC03-3.3SK/SMT RAC03-05SK/SMT








BASIC CHARACTERISTICS (measured @ T_{AMB}= 25°C, nom. V_{IN}, full load and after warm-up unless otherwise stated)


all others




REGULATIONS (measured @ T _{AMB} = 25°C, nom. V _{IN} , full load and after warm-up unless otherwise stated)		
Parameter	Condition	Value
Output Accuracy		±3.0% typ.
Line Regulation	low line to high line, full load	±2.5% typ.
Load Regulation (4)	10% to 100% load	2.5% typ.
Transient Response	25% load step change	4.0% max.
	recovery time	500µs max.

Note4: Operation below 10% load will not harm the converter, but specifications may not be met

Deviation vs. Load








PROTECTIONS (measured @ T _{AMB} = 25	°C, nom. V _№ , full lo	bad and after wa	arm-up unless otherwise s	tated)
Parameter	Туре			Value
Input Fuse (5)		interna	al	fusible resistor
Limited Powr Source (LPS)				yes
Short Circuit Protection (SCP)		below 100	DmΩ	hiccup mode, auto recovery
Over Current Protection (OCP)				hiccup mode, auto recovery
Over Voltage Category (OVC)				OVC II
Class of Equipment				Class II
			according to 60335-1	3kVAC
Isolation Voltage ⁽⁶⁾	I/P to O/P	1 minute	according to 62368-1	4kVAC
		according to 61558	4.2kVAC	
Isolation Resistance	V _{ISO} = 500VDC			1GΩ min.
Isolation Capacitance	I/P to O/P, 100kHz/0.1V		100pF max.	
Insulation Grade				reinforced


Note5: For system integration with DC operation, consider a suitable DC fuse in front of the input Note6: For repeat Hi-Pot testing, reduce the time and/or the test voltage

ENVIRONMENTAL (measured @ T _{AI}	мв= 25°C, nom. V№, full load and	after warm-up unless otherwise stated)
Parameter	Condition		Value
Operating Ambient Temperature Range	@ natural convection (0.1m/s) with derating, refer to "Derating Graph"		-40°C to +80°C
Maximum Case Temperature			+95°C
Temperature Coefficient			±0.05%/K
Operating Altitude	accord	ding to 62368-1	5000m
Operating Altitude	according to 60335-1		6000m
Operating Humidity	non-condensing		20-90% RH max.
Pollution Degree			PD2
Vibration	according to MIL-STD-202G		10-500Hz, 2G, 10min.: 1cycle, period / 60min. each along x,y,z axes
		T _{AMB} = +25°C	>1977 x 10 ³ hours
MTBF	according to MIL-HDBK-217, G.B.	T _{AMB} = +30°C	>1895 x 10 ³ hours
		$T_{AMB} = +40^{\circ}C$	>1794 x 10 ³ hours
Design Lifetime	230VAC/60Hz and full load	T_{AMB} = +25°C	>40 x 10 ³ hours

Derating Graph

(@ Chamber and natural convection 0.1m/s)








SAFETY & CERTIFICATIONS	Report Number	Standard
Certificate Type (Safety)		UL62368-1:2014, 2nd Edition
Audio/Video, information and communication technology equipment - Part1: Safety requirements	E491408-A6012-UL	CAN/CSA C22.2 No. 62368-1-14, 2nd Edition
Audio/Video, information and communication technology equipment - Part1: Safety requirements (CB Scheme)	231023001	IEC62368-1:2014, 2nd Edition
Audio/Video, information and communication technology equipment - Part1: Safety requirements (LVD)	231023001	EN62368-1:2014 + A11:2017
Household and similar electrical appliances - Safety - Part 1: General requirements (CB Scheme)		IEC60335-1:2010 + C1:2016, 5th Edition
Household and similar electrical appliances – Safety – Part 1: General requirements (LVD)	LCS190408025CS	EN60335-1:2012 + A13:2017
Measurement methods for electromagnetic fields of household appliances and similar apparatus with regard to human exposure	20013040002000	EN62233:2008
Safety of power transformers, power supplies, reactors and similar products for supply voltages up to 1100 V (CB Scheme)	50237373-001	IEC61558-1:2005 2nd Edition + A1:2009
Safety of power transformers, power supplies, reactors and similar products for supply voltages up to 1100 V	50237374-001	EN61558-1:2005 + A1:2009
Safety of transformers, reactors, power supply units and similar products for supply voltages up to 1100 V Part 2-16: Particular requirements and tests for switch mode power supply units and transformers for switch mode power supply units (CB Scheme)	50237373-001	IEC61558-2-16:2009 1st Edition + A1:2013
Safety of transformers, reactors, power supply units and similar products for supply voltages up to 1100 V Part 2-16: Particular requirements and tests for switch mode power supply units and transformers for switch mode power supply units	50237374-001	EN61558-2-16:2009 + A1:2013
RoHS2		RoHS 2011/65/EU + AM2015/863
EMC Compliance	Condition	Standard / Criterion
Low voltage power supplies, d.c. output - Part 3: Electromagnetic compatibility		IEC/EN61204-3:2008, Class B
Electromagnetic compatibility of multimedia equipment - Emission requirements (7)		EN55032:2015, Class B
Information technology equipment - Immunity characteristics - Limits and methods of measurement	LCS190408054BE	EN55024:2010 + A1:2015
Electromagnetic compatibility - Requirements for household appliances, electric tools and similar apparatus - Part 1: Emission $^{(7)}$	L0010040004DL	EN55014-1:2006 + A2:2011, Class B
Electromagnetic compatibility - Requirements for household appliances, electric tools and similar apparatus - Part 2: Immunity		EN55014-2:2015
ESD Electrostatic discharge immunity test	Air: ± 2 , 4, 8kV Contact: ± 2 , 4kV	IEC61000-4-2:2008 , Criteria B EN61000-4-2:2009, Criteria B
Radiated, radio-frequency, electromagnetic field immunity	10V/m (80-1000MHz) 3V/M (1.4-2GHz) 1V/m (2-2.7GHz)	IEC61000-4-3:2006 + A1:2007 , Criteria A EN61000-4-3:2006 + A1:2009, Criteria A
Fast Transient and Burst Immunity	AC & DC Port: ±2kV	IEC/EN61000-4-4:2012, Criteria B
Surge Immunity	AC Port: ±1kV DC Port: ±0.5kV	IEC/EN61000-4-5:2014 + A1:2017, Criteria B
Immunity to conducted disturbances, induced by radio-frequency fields	AC & DC Port: 10V	IEC61000-4-6:2013, Criteria A EN61000-4-6:2014, Criteria A
Power Magnetic Field Immunity	50Hz, 30A/m	IEC61000-4-8:2009, Criteria A EN61000-4-8:2010, Criteria A
Velkara Diaz	100%	IEC/EN61000-4-11:2004 + A1:2017, Criteria B
Voltage Dips	60%, 30% and 20%	IEC/EN61000-4-11:2004 + A1:2017, Criteria C
Voltage Interruptions	>95%	IEC/EN61000-4-11:2004 + A1:2017, Criteria C
Limits of Harmonic Current Emissions		EN61000-3-2:2014
Limits of Voltage Fluctuations & Flicker		EN61000-3-3:2013
Limitations on the amount of electromagnetic interference allowed from digital and electronic devices		FCC 47 Part 15 Subpart B

Note7: If output is connected to GND, please contact RECOM tech support for further information



DIMENSION & PHYSICAL CHARACTERISTICS		
Parameter	Туре	Value
	case/baseplate	black plastic, (UL94 V-0)
Materials	potting	silicone, (UL94 V-0)
	PCB	FR4, (UL94 V-0)
Dimension (LxWxH)		27.7 x 23.7 x 19.0mm
		1.1 x 0.9 x 0.8 inch
Weight		15.5g typ.
		0.034 lbs

Dimension Drawing (mm)




 $\begin{array}{ll} \mbox{Tolerance:} & xx.x=\pm0.5\mbox{mm} \\ & xx.xx=\pm0.25\mbox{mm} \end{array}$

6.35




DIMENSION & PHYSICAL CHARACTERISTICS

Recommended Footprint Details (Top view)



Tolerance: $xx.x = \pm 0.5mm$ $xx.xx = \pm 0.25mm$

SOLDER PROFILE



Time [s]

PACKAGING INFORMATION			
Parameter	Туре	Value	
	reel (diameter + width)	Ø380.0 + 60.0mm	
Packaging Dimensions (LxWxH)	tape and reel (carton)	435.0 x 435.0 x 73.0mm	
Tape Width		56mm	
Packaging Quantity	reel	50pcs	
Storage Temperature Range		-40°C to +85°C	
Storage Humidity	non-condensing	20-95% RH max.	
Moisture Sensitive Level		2	

The product information and specifications may be subject to changes even without prior written notice. The product has been designed for various applications; its suitability lies in the responsibility of each customer. The products are not authorized for use in safety-critical applications without RECOM's explicit written consent. A safety-critical application is an application where a failure may reasonably be expected to endanger or cause loss of life, inflict bodily harm or damage property. The applicant shall indemnify and hold harmless RECOM, its affiliated companies and its representatives against any damage claims in connection with the unauthorized use of RECOM products in such safety-critical applications.