Features

Regulated Converter

- 80 to 305VAC input voltage range
- 150% peak power capability
- Wide temperature range: -40°C to +90°C
- No load power consumption <150mW
- Household and ITE certified
- 4kVac isolation
- Operating Altitude up to 5000m

Description

The RACO4-K/277 series delivers an uncompromising 4 watts of continuous output power (6W peak) in harsh industrial and household environments. These modules deliver full load output power from -40°C to 75°C across the entire input range of 80VAC to 305VAC and are certified for operation with power derating up to 90°C air ambient. A peak load capability of up to 150% supports dynamic power demands of applications. This series of fully encapsulated AC/DC modules is a complete solution without the need for external components which supports Ecodesign Lot 6 standby mode operation for worldwide applications in automation, industry 4.0, IoT, household, and home automation. With international safety and EMC certifications for industrial, domestic, ITE, and household applications, these are some of the most versatile power modules on the market. Due to their reinforced class II installation rating for floating outputs and their significantly wide margin to class B emissions compliance without external components and a certified 4kV AC (5.75kV DC) isolation, these are the easiest to use modular power solutions in the industry.


Selection Guide					
Part Number	Input Voltage Range [(VAC]	Output Voltage [VDC]	Output Current ⁽¹⁾ [mA]	Efficiency typ. ⁽²⁾ [%]	Max. Capacitive Load [μF)
RAC04-3.3SK/277	80-305	3.3	1200	73	10000
RAC04-05SK/277	80-305	5	800	76	7200
RAC04-12SK/277	80-305	12	333	78	1000
RAC04-15SK/277	80-305	15	267	80	820
RAC04-24SK/277	80-305	24	167	80	220

Notes:

Note1: Refer to "Line Derating" graph

Note2: Measured @ 230VAC/50Hz at +25°C with constant resistant mode at full load

Model Numbering



Specifications (measured @ Ta= 25°C, nom. Vin, full load and after warm-up unless otherwise stated)

Parameter	Condition		Min.	Тур.	Max.
Input Voltage Dange (3)	nom. Vin= 277VAC		80VAC		305VAC
Input Voltage Range (3)			110VDC		390VDC
1 10 1	115VAC				250mA
Input Current	230VAC				100mA
Inrush Current	cold start at +25°C	115VAC			10A
infush current		230VAC			20A
No load Power Consumption	80-305VAC, 50/60Hz			100mW	150mW
ErP Standby Mode Conformity	Innut Dawer	0.5W			0.3W
(Output Load Capability)	Input Power=	1W			0.65W



RAC04-K/277

4 Watt Single Output



















IEC60950-1 certified
IEC62368-1certified
UL62368-1 certified
CSA/CAN C22.2 No. 62368-1-14 certified
EN62368-1 compliant
EN60335-1 compliant
EN61010-1 compliant

IEC/EN61558-1 compliant IEC/EN61558-2-16 compliant

EN55032 compliant

EN55024 compliant

EN55014-1 /-2 compliant IEC/EN61204-3 compliant

FCC 47 Part 15 CB Report

www.recom-power.com REV: 3/2021 PA-1



Series


Specifications (measured @ Ta= 25°C, nom. Vin, full load and after warm-up unless otherwise stated)


BASIC CHARACTERISTICS (continuous)				
Parameter	Condition	Min.	Тур.	Max.
Input Frequency Range	AC input	47Hz		63Hz
Start-up Time			20ms	
Rise Time			10ms	
Hold up time	115VAC		20ms	
Hold-up time	230VAC		80ms	
Minimum Load		0%		
Power Factor	115VAC	0.6		
ruwei raciui	230VAC	0.45		
Internal Operating Frequency	full load		130kHz	
Output Ripple and Noise (4)				1% of nom. Vol


Notes:

Note3: The products were submitted for safety files at AC-Input operation


Note4: Measurements are made with a $1.0\mu F$ MLCC and a $10\mu F$ MLCC across output








Output Load [%]





Series


Specifications (measured @ Ta= 25°C, nom. Vin, full load and after warm-up unless otherwise stated)




REGULATIONS				
Parameter	Condition	Value		
Output Accuracy		±1.0% typ.		
Line Regulation		±0.5% typ.		
Load Regulation		1.0% typ.		
Transient Response	25% load step change	4.0% max.		
וומווטופווג חפטשטווטפ	recovery time	500µs		

Deviation vs. Load

(80-305VAC)








Series

Specifications (measured @ Ta= 25°C, nom. Vin, full load and after warm-up unless otherwise stated)



PROTECTIONS				
Parameter	T	ype	Value	
Input Fuse (5)	int	ernal	T1A, slow blow	
Short Circuit Protection (SCP)			Hiccup Mode, auto recovery	
Over Voltage Protection (OVP)			125% - 195%, Hiccup Mode	
Over Voltage Category (OVC)			OVCII	
Over Current Protection (OCP)			150% - 210%, Hiccup Mode	
Class of Equipment			Class II	
Isolation Voltage (safety certified) (6)	I/P to O/P	1 minute	5.75kVDC 4kVAC	
Isolation Resistance	Viso= 500VDC		1GΩ min.	
Isolation Capacitance	I/P to O/P	100kHz, 0.1V	100pF max.	
Insulation Grade			reinforced	
Leakage Current		<u> </u>	0.25mA max.	

Notes:

Note5: Refer to local safety regulations if input over-current protection is also required. Recommended fuse: slow blow type

Note6: For repeat Hi-Pot testing, reduce the time and/or the test voltage.

continued on next page



Series


Specifications (measured @ Ta= 25°C, nom. Vin, full load and after warm-up unless otherwise stated)

Peak Load Capability (7)

Peak Load Calculation

 P_{nom} = nom. output power [W] = peak output power (6W max.) [W] = recovery output power [W]= peak time set (10s max.) [s] = recovery time (min. $4 \times t_1$) [s]

 $\mathbf{P_r} = \frac{P_{\text{nom}} x (t_1 + t_2) - P_p x t_1}{t_2 x k}$



Practical Example:

= safety factor 1.3

Take the RAC04-05SK/277 at 230VAC input Voltage and full load at $T_{AMR} = 50$ °C (4W).

[]

 $P_{nom.} = please refer to derating graph (4W)$

=6W

= 10s t_1 = min. 4 x t_1 $P_{r} = \frac{4 \times (10 + 4 \times 10) - (6 \times 10)}{4 \times 10 \times 1.3} = \underline{2.69W}$

= 1.3

Notes:

Peak load calculation valid for 100-305VAC Note7:

ENI/IDONIMENTAI


ENVIRONMENTAL				
Parameter	Condition			Value
On avating Tampagatura Danga	ure Range @ natural convection 0.1m/s full load refer to "Derating Graph"		-40°C to +75°C	
Operating Temperature Range			ating Graph"	-40°C to +90°C
Maximum Case Temperature				+100°C
Temperature Coefficient				±0.02%/K
Operating Altitude (8)	according to IEC62368-1 (EN60335-1)		i-1)	5000m (4000m)
Operating Humidity	non-cond	non-condensing		20% - 95%, RH max.
Pollution Degree				PD2
Vibration	according to MIL-STD-202G			10-500Hz, 2G 10min. / 1 cycle, periode 60min. each along x, y, z axis
MTBF	according to MIL-HDBK-217F, G.B		+25°C	>2271 x 10 ³ hours
IVIIDF			+40°C	>1696 x 10 ³ hours
Desire History	230VAC		+25°C	125 x 10 ³ hours
			+70°C	51 x 10 ³ hours
Design Lifetime	277\/\C		+25°C	105 x 10 ³ hours
	277VAC		+70°C	37 x 10 ³ hours

Notes:


Note8: Recognized by safety agency for safe operation up to 5000m. High altitude operation may impact the performance and lifetime. Please contact RECOM tech support for advice.

Derating Graph

(@ Chamber and natural convection 0.1m/s)



Line Derating





Series

Specifications (measured @ Ta= 25°C, nom. Vin, full load and after warm-up unless otherwise stated)

Certificate Type	Report Number	Standard
Audio/video, information and communication technology equipment - Safety requirements	E224736	UL62368-1:2014, 2nd Editio CAN/CSA C22.2 No. 62368-1-14, 2nd Editio
nformation Technology Equipment, General Requirements for Safety (CB)		IEC60950-1:2005 + A2:2013, 2nd Editio
nformation Technology Equipment, General Requirements for Safety	E491408-A6-CB-1	EN60950-1:2006 + A2:201
Audio/video, information and communication technology equipment - Safety requirements (CB)	E491408-A6011-CB-1	IEC62368-1:2014, 2nd Editio
Audio/video, information and communication technology equipment - Safety requirements (LVD)		EN62368-1:2014 + A11:201
Household and similar electrical appliances - Safety - Part 1: General requirements (LVD)		EN60335-1:2012 + A1:201
Safety of power transformers, power supplies, reactors and similar products for supply voltages up to 1100 V		IEC61558-1:2005 2nd Edition + A1:200 EN61558-1:2005 + A1:200
Safety of transformers, reactors, power supply units and similar products for supply voltages up o 1100 V - Part 2-16: Particular requirements and tests for switch mode power supply units and ransformers for switch mode power supply units (LVD)		IEC61558-2-16:2009 + A1:2013, 1st Editio EN61558-2-16:2009 + A1:201
Safety requirements for electrical equipment for measurement, control and laboratory use - Part 1: General requirements (LVD)		EN61010-1:201
RoHS2		RoHs-2011/65/EU + AM-2015/86
EMC Compliance (Household)	Report / File Number	Standard / Criterio
Electromagnetic compatibility - Requirements for household appliances, electric tools and similar apparatus - Part 1: Emission ⁽⁸⁾		EN55014-1:2006 + A2:201
Electromagnetic compatibility - Requirements for household appliances, electric tools and similar apparatus - Part 2: Immunity		EN55014-2:201
ESD Electrostatic discharge immunity test	Air ±8kV; Contact ±4kV	IEC61000-4-2:2008, Criteria E
Fast Transient and Burst Immunity	AC Power Port: ±1.0kV	IEC61000-4-4:2012, Criteria E
Surge Immunity	AC Power Port: L-N ±1.0kV	IEC61000-4-5:2014, Criteria E
Immunity to conducted disturbances, induced by radio-frequency fields	AC Power Port: 3V	EN61000-4-6:2013, Criteria A
Voltage Dips and Interruptions	Voltage Dips: 100% 60%	EN61000-4-11:2004, Criteria (EN61000-4-11:2004, Criteria (
EMC Compliance (Multimedia)	Condition	Standard / Criterior
ow voltage power supplies, d.c. output - Part 3: Electromagnetic compatibility		IEC/EN61204-3:2000, Class
Electromagnetic compatibility of multimedia equipment - Emission requirements ⁽⁹⁾		EN55032:2015, Class
nformation technology equipment - Immunity characteristics - Limits and methods of measurement		EN55024:2010 + A1:201
ESD Electrostatic discharge immunity test	Air ±2,4,8kV; Contact ±4kV	IEC61000-4-2:2008, Criteria E
	10V/m (80 - 1000MHz)	IEC61000-4-3, Criteria A
Radiated, radio-frequency, electromagnetic field immunity test	3V/m (1800MHz, 2600Mhz, 3500MHz, 5000MHz)	IEC61000-4-3:2006 + A2:2010, Criteria A
Fort Transition to and Discontinuous like	AC Power Port: ±2.0kV	IEC61000-4-4, Criteria E
Fast Transient and Burst Immunity	AC Power Port: ±1.0kV	IEC61000-4-4:2012, Criteria A
Surge Immunity	AC Power Port: L-N ±1.0kV	IEC61000-4-5:2014, Criteria A
Immunity to conducted disturbances, induced by radio-frequency fields	AC Power Port: 10V	IEC61000-4-6, Criteria A
Voltage Dips and Interruptions	100% / 30% Voltage Dips: 70% 40% Interruptions: >95%	IEC61000-4-11:2004, Criteria I IEC61000-4-11:2004, Criteria I IEC61000-4-11:2004, Criteria I IEC61000-4-11:2004, Criteria I
Limits of Voltage Fluctuations & Flicker	intorruptions. 200/0	EN61000-3-3:201
Limits of voltage Fluctuations & Flicker Limitations on the amount of electromagnetic interference allowed from digital and electronic devices		FCC 47 Part 15 Subpart B:2017, Class

www.recom-power.com REV.: 3/2021 PA-6





Series


Specifications (measured @ Ta= 25°C, nom. Vin, full load and after warm-up unless otherwise stated)


DIMENSION and PHYSICAL CHARACTERISTICS				
Parameter	Туре	Value		
	case/baseplate	plastic, (UL94 V-0)		
Material	potting	silicone, (UL94 V-0)		
	PCB	FR4, (UL94 V-0)		
Dimension (LxWxH)		36.7 x 27.2 x 17.4mm		
Weight		30g typ.		


Dimension Drawing (mm)













Pinning information

Pin#	Single	
1	NC	
2	VAC in (N)	
3	VAC in (L)	
4	NC	
5	-Vout	
6 +Vout		

NC= no connection

Tolerance: $xx.x = \pm 0.5$ mm

 $xx.xx = \pm 0.25mm$

PACKAGING INFORMATIONParameterTypeValuePackaging Dimension (LxWxH)tube506.4 x 29.8 x 25.5mmPackaging Quantity12pcsStorage Temperature Range-40°C to +85°CStorage Humiditynon-condensing20% to 90% RH max.

The product information and specifications may be subject to changes even without prior written notice. The product has been designed for various applications; its suitability lies in the responsibility of each customer. The products are not authorized for use in safety-critical applications without RECOM's explicit written consent. A safety-critical application is an application where a failure may reasonably be expected to endanger or cause loss of life, inflict bodily harm or damage property. The applicant shall indemnify and hold harmless RECOM, its affiliated companies and its representatives against any damage claims in connection with the unauthorized use of RECOM products in such safety-critical applications.