Features

Regulated

Converter

Efficiency up to 76%

Isolated output 3kVAC / 1 min

• 35mW max. no load power consumption

- SCP, OVP protection
- Wide operating temperature range: -40°C to +85°C
- Universal input 85-305VAC

RECOM AC/DC Converter

RAC02-SE/277

2 Watt Single Output

















PREFERRED ALTERNATIVES

Please consider this alternatives:

RAC02E-K/277

IEC/EN60950-1 certified CAN/CSA-22.2 No. 60950 certified UL60950-1 certified EN60335-1 certified EN55032 certified EN55024 certified EN55014 certified

Description

The ultra-compact RAC02-SE/277 modules are available with output voltages of 3.3, 5, 12 and 24V, and the input-to-output isolation is 3kVAC/1min. With a standby consumption of 35mW maximum, the mini power supplies are particularly suitable for energy-saving sleep mode and standby applications. Because of its compact design (height <18mm), it is a versatile solution for home automation and other similar applications. Complete with an integrated input filter, the series has enhanced EMI performance and complies with EN55032, class B. The mini power supplies are also protected against short circuit with fully automatic restart after the error has been solved. The converters are EN/UL60950-1 certified and come complete with a 3 year warranty.

Selection Guide						
Part Number	nom. Input Voltage Range [VAC]	Output Voltage [VDC]	Output Current [mA]	Efficiency typ ⁽¹⁾ [%]	Max. Capacitive Load ⁽²⁾ [μF]	
RAC02-3.3SE/277	100-277	3.3	600	67	12000	
RAC02-05SE/277	100-277	5	400	70	5500	
RAC02-12SE/277	100-277	12	167	73	500	
RAC02-24SE/277	100-277	24	83	76	160	

Notes:

Note1: Efficiency is tested at nominal input and full load at +25°C ambient Note2: Max Cap Load is tested by minimum input and constant resistor load

Model Numbering



Ordering Examples:

RAC02-05SE/277 2 Watt 5Vout Single Output RAC02-12SE/277 2 Watt 12Vout Single Output



Series

Specifications (measured @ Ta= 25°C, nom. Vin (115/230VAC), full load and after warm-up unless otherwise stated)

BASIC CHARACTERISTICS						
Parameter	Condition		Min.	Тур.	Max.	
Input Voltage Range (3,4)	nom. Vin = 230VAC		85VAC 120VDC	277VAC	305VAC 430VDC	
Input Current	115VAC 230VAC			47mA 30mA		
Inrush Current	cold start at +25°C	115VAC 230VAC			15A 30A	
No load Power Consumption	85-305VAC, 47-63Hz				35mW	
Input Frequency Range	AC Input		47Hz		440Hz	
Minimum Load (5)				2%		
Hold-up Time	115VAC		18ms			
Internal Operating Frequency	100% load at nominal Vin			55kHz		
Output Ripple and Noise (6)	20MHz BW	3.3V all others			300mVp-p 250mVp-p	

Notes:

Note3: The products were submitted for safety files at AC-Input operation


Note4: No line derating required


Note5: Operation below 2% load will not harm the converter, but specifications may not be met

Note6: Ripple and Noise is the maximum peak-to-peak voltage value measured at the output with a 20MHz bandwidth, at rated line voltage

at full load. And with a 47µF low-ESR electrolytic capacitor in parallel with a 0.1µF ceramic capacitor across output

Efficiency vs. Load





REGULATIONS				
Parameter	Condition	Value		
Output Accuracy (7)		±6.0% max.		
Line Regulation	low line to high line, full load	±1.5% max.		
Load Regulation	2% to 100% load	6.0% typ.		

Notes:


Note7: Includes initial voltage accuracy, thermal drift, line regulation and load regulation at rated input voltage and load conditions

continued on next page



Series

Specifications (measured @ Ta= 25°C, nom. Vin, full load and after warm-up unless otherwise stated)




PROTECTIONS					
Parameter	Ту	ре	Value		
Short Circuit Protection (SCP)	below 1	00mΩ	continuous, automatic recovery		
Over Voltage Protection (OVP)	zener dio	de clamp	110% - 140%		
Over Voltage Category			OVCII		
Over Current Limit			110% - 190%		
Isolation Voltage	tested for 1 minute	I/P to O/P	3kVAC		
Isolation Resistance			1GΩ min.		
Leakage Current	85-305VAC, 47-63Hz		10μA max.		

Notes:

Refer to local wiring regulations if input over-current protection is also required. Recommended fuse: T1A slow blow type Note8:

Note9: An external MOV is recommended. The Varistor should comply with IEC-61051-2. e.g. EPCOS S 14 Series

Protection Circuit




ENVIRONMENTAL					
Parameter	Conditi	Condition		Value	
Operating Temperature Range	@ natural convection 0.1 m/s, 140, 206	EVA C	full load	-40°C to +75°C	
Operating reinperature hange	@ natural convection 0.1m/s, 140-305VAC		efer to derating graph	-40°C to +85°C	
Maximum Case Temperature				+105°C	
Thermal Impedance				8.5°C/W typ.	
Operating Humidity	non-condensing		5% - 95% RH max.		
Vibration	according to MIL-STD-202G stand		according to MIL-STD-202G standard		
MTBF	according to MIL-HDBK-217F, G.B.	+25°C	115VAC	2238 x 10 ³ hours	
INTO	according to Mile-HDBN-2171, d.B.	T23 0	230VAC	1670 x 10 ³ hours	
continued on next page					



Series

Specifications (measured @ Ta= 25°C, nom. Vin, full load and after warm-up unless otherwise stated)



SAFETY AND CERTIFICATIONS		
Certificate Type (Safety)	Report / File Number	Standard
Information Technology Equipment - General Requirments for Safety (CB Scheme)	L0339L26-CB-1-B4	IEC60950-1:2005, 2nd Edition + A2:2013 EN60950-1:2006 + A2:2013
Information Technology Equipment, General Requirements for Safety	E224736-A24-UL	UL60950-1, 2nd Edition, 2014 CAN/CSA-C22.2 60950-1, 2nd Edition, 2014
Household and similar electrical appliances - Safety - Part 1: General requirements	L0339L26-B2-L	EN60335-1:2012 + A11:2014
EAC Safety of Low Voltage Equipment	RU-AT.49.09571	TP TC 004/2011
RoHS2+		RoHS-2011/65/EU + AM-2015/863
EMC Compliance (Industrial)	Condition	Standard / Criterion
Electromagnetic compatibility of multimedia equipment – Emission Requirements		EN55032:2015, Class E
Information technology equipment - Immunity characteristics - Limits and methods of measurement		EN55024:2010
ESD Electrostatic discharge immunity test	±8kV air, ±4kV contact	EN61000-4-2:2009, Criteria E
Radiated, radio-frequency, electromagnetic field immunity test	3V/m	EN61000-4-3:2006 + A2:2010, Criteria A
Fast Transient and Burst Immunity	AC Power Port: ±1.0kV	EN61000-4-4:2012, Criteria A
Power Magnetic Field Immunity	50Hz, 1A/m	EN61000-4-8:2010, Criteria A
Voltage Dips and Interruptions	Voltage Dips >95%	EN61000-4-11:2004, Criteria A
	Voltage Dips 30%	EN61000-4-11:2004, Criteria A
	Voltage Interruptions >95%	EN61000-4-11:2004, Criteria E
Limits of Voltage Fluctuations & Flicker		EN61000-3-3:2013
EMC Compliance (Household)	Condition	Standard / Criterion
Electromagnetic compatibility - Requirements for household appliances, electric tools and similar apparatus - Part 1: Emission		EN55014-1:2006+A2:2011
Information technology equipment - Immunity characteristics - Limits and methods of measurement		EN55014-2:2015
ESD Electrostatic discharge immunity test	±8kV air, ±4kV contact	IEC61000-4-2:2008, Criteria A
Radiated, radio-frequency, electromagnetic field immunity test	3V/m	IEC61000-4-3:2006 + A2:2010, Criteria A
Fast Transient and Burst Immunity	AC Power Port: ±1kV DC Output: ±0.5kV	IEC61000-4-4:2012, Criteria A
continued on r	next page	



Series

Specifications (measured @ Ta= 25°C, nom. Vin, full load and after warm-up unless otherwise stated)


SAFETY AND CERTIFICATIONS				
EMC Compliance (Household)	Condition	Standard / Criterion		
Surge Immunity	AC Power Port:L to N ±2kV DC Output: L to N ±1kV	IEC61000-4-5:2014, Criteria B		
Immunity to conducted disturbances, induced by radio-frequency fields	3 Vr.m.s.	IEC61000-4-6:2013, Criteria A		
Voltage Dips and Interruptions	Voltage Dips >95%	IEC61000-4-11:2004, Criteria B		
	Voltage Dips 30%	IEC61000-4-11:2004, Criteria C		
	Voltage Interruptions >95%	IEC61000-4-11:2004, Criteria C		
Limits of Harmonic Current Emissions		EN61000-3-2:2014		
Limits of Voltage Fluctuations & Flicker		EN61000-3-3:2013		


DIMENSION AND PHYSICAL CHARACTERISTICS				
Parameter	Туре	Value		
Material	case	black plastic, (UL94V-0)		
Material	potting	silicone, (UL94V-0)		
Dimension (LxWxH)		33.70 x 22.20 x 17.75mm		
Weight		24.5g typ.		

Dimension Drawing (mm)



33.7





Pin Connections

Pin #	Single		
_ 1	VAC in (N)		
2	VAC in (L)		
3	-Vout		
4	+Vout		

 $\begin{array}{lll} \mbox{Tolerance:} & \mbox{xx.x=} & \pm 0.5 \mbox{mm} \\ & \mbox{xx.xx=} & \pm 0.35 \mbox{mm} \\ \mbox{Pin width:} & \pm 0.05 \mbox{mm} \end{array}$

PACKAGING INFORMATION				
Parameter	Туре	Value		
Packaging Dimension (LxWxH)	tube	520.0 x 37.0 x 28.0mm		
Packaging Quantity		22pcs		
Storage Temperature Range		-40°C to +85°C		

The product information and specifications may be subject to changes even without prior written notice. The product has been designed for various applications; its suitability lies in the responsibility of each customer. The products are not authorized for use in safety-critical applications without RECOM's explicit written consent. A safety-critical application where a failure may reasonably be expected to endanger or cause loss of life, inflict bodily harm or damage property. The applicant shall indemnify and hold harmless RECOM, its affiliated companies and its representatives against any damage claims in connection with the unauthorized use of RECOM products in such safety-critical applications.