Features

Regulated Converter

- Wide input range 85-305VAC
- Standby mode optimized (eco design Lot 6)
- High efficiency over the entire load range
- Operating temperature range: -40°C to +90°C
- Class II installations (without FG)
- Overvoltage and overcurrent protected
- EMC compliant without external components

Description

The RAC3.5-K/277 series are multipurpose 3.5 watt AC/DC power supplies for enhanced mains input conditions from 85VAC up to 305VAC with an extra wide operating temperature range from -40°C to +90°C. These modules are designed to supply worldwide applications in automation, Industry 4.0, IoT, household and smart buildings. For worldwide use they come with international safety certifications for industrial, domestic and ITE as well as household standards. With fully protected outputs, as well as EMC class B emissions compliance without any external components, these are the easiest to use modular power solutions in the industry.

Selection Guide					
Part Number	Input Voltage Range [VAC]	Output Voltage [VDC]	Output Current [mA]	Efficiency typ ⁽¹⁾ [%]	Max. Capacitive Load ⁽²⁾ [μF]
RAC3.5-3.3SK/277	85-305	3.3	1060	77	10000
RAC3.5-05SK/277	85-305	5	700	80	8000
RAC3.5-12SK/277	85-305	12	291	83	1500
RAC3.5-15SK/277	85-305	15	233	83	1000
RAC3.5-24SK/277	85-305	24	146	84	330

Notes:

Note1: Efficiency is tested at nominal input and full load at +25°C ambient Note2: Max Cap Load is tested at nominal input and full resistive load

Model Numbering



Ordering Examples:

RAC3.5-05SK/277 3.5 Watt 5Vout Single Output RAC3.5-24SK/277 3.5 Watt 24Vout Single Output



RAC3.5-K/277

3.5 Watt Single Output





















UL62368-1 certified EN62368-1 certified IEC/EN60335-1 certified EN62233 certified IEC/EN61558-1 certified IEC/EN61558-2-16 certified EN55032 compliant EN55014-1(-2) compliant CB Report



Series

Specifications (measured @ Ta= 25°C, nom. Vin, full load and after warm-up unless otherwise stated)

BASIC CHARACTERISTICS					
Parameter	Condi	Condition		Тур.	Max.
Internal Input Filter					Pi type
Input Voltage Range (3,4)	nom. Vin =	277VAC	85VAC 120VDC	277VAC	305VAC 430VDC
Input Current	115V 230V 277V	'AC		110mA 80mA 60mA	
Inrush Current	cold start at +25°C	115VAC 230VAC 277VAC			15A 30A 35A
No Load Power Consumption					100mW
ErP Lot 6 Standby Mode Conformity (Output Load Capability)	Innut Power—	0.5W 1.0W			0.34W 0.70W
Input Frequency Range			47Hz		63Hz
Minimum Load			0%		
Power Factor	115V 230V 277V	/AC	0.50 0.40 0.35		
Start-up Time				20ms	
Rise Time				10ms	
Hold-up Time	230\	115VAC 230VAC 277VAC		20ms 25ms 90ms	
Internal Operating Frequency	100% load at	nominal Vin		130kHz	
Output Ripple and Noise (5)	20MHz BW	3.3.5Vout		60mVp-p 1% of Vout	


Notes:


Note3: The products were submitted for safety files at AC-Input operation

Note4: Refer to "Line Derating"

Note5: Measurements are made with a 0.1µF MLCC & 10µF E-cap in parallel across output. (low ESR)

Efficiency vs. Load







Series

Specifications (measured @ Ta= 25°C, nom. Vin, full load and after warm-up unless otherwise stated)


REGULATIONS		
Parameter	Condition	Value
Output Accuracy		±1.0% typ.
Line Regulation	low line to high line, full load	±0.5% typ.
Load Regulation (6)	10% to 100% load	1.0% typ.
Transient Response	25% load step change	4.0% max.
	recovery time	500µs typ.


Notes:

Note6: Operation below 10% load will not harm the converter, but specifications may not be met

Deviation vs. Load

(at 115VAC, 230VAC, 277VAC)





PROTECTIONS			
Parameter	Ту	pe	Value
Input Fuse (7)	inte	rnal	T1A, slow blow
Short Circuit Protection (SCP)	below 1	100mΩ	hiccup, automatic restart
Over Voltage Protection (OVP)			125% - 195%, latch of mode
Over Voltage Category			OVCII
Over Current Protection (OCP)			175% - 275%, hiccup mode
Class of Equipment			Class II
Isolation Voltage (8)	I/P to O/P	1 minute	4.2kVAC
Isolation Resistance	1/P 10 0/P	Viso= 500VDC	1G Ω min.
Isolation Capacitance			100pF max.
Insulation Grade			reinforced
Leakage Current			0.25mA max.

Notes:

Note7: Refer to local safety regulations if input over-current protection is also required


Note8: For repeat Hi-Pot testing, reduce the time and/or the test voltage

continued on next page



Series

Specifications (measured @ Ta= 25°C, nom. Vin, full load and after warm-up unless otherwise stated)



ENVIRONMENTAL				
Parameter	Condition			Value
Operating Temperature Penge	@ natural convection 0.1m/s	full load		-40°C to +80°C
Operating Temperature Range		refer to "De	rating Graph"	-40°C to +90°C
Maximum Case Temperature				+95°C
Temperature Coefficient				0.05%/K
Operating Altitude (9)				5000m
Operating Humidity	non-cond	lensing		5% - 95% RH max.
Pollution Degree				PD2
Vibration	according to M	L-STD-202G		10-500Hz, 2G 10min./1cycle, period 60min. each along x,y,z axis
MTBF	according to MIL-HDBK-2	17F, G.B.	+25°C +40°C	>2252 x 10 ³ hours >1806 x 10 ³ hours
	230VAC		+25°C +70°C	125 x 10 ³ hours 34 x 10 ³ hours
Design Lifetime	277VAC		+25°C +70°C	105 x 10 ³ hours 27 x 10 ³ hours


Notes:

Note9: Recognized by UL for safe operation up to 5000m. High altitude operation may impact the performance and lifetime.


Contact RECOM tech support for advice

Derating Graph

(@ Chamber and natural convection 0.1m/s)



Line Derating





Series

Specifications (measured @ Ta= 25°C, nom. Vin, full load and after warm-up unless otherwise stated)

SAFETY AND CERTIFICATIONS		
Certificate Type (Safety)	Report / File Number	Standard
Audio/Video, information and communication technology equipment - Part 1: Safety requirements	E491408-A6004-UL	UL62368-1, 2nd Edition, 2014-12-01 CAN/CSA-C22.2 No. 62368-1-14, 2nd Edt., 2014-12
Audio/Video, information and communication technology equipment - Part 1: Safety requirements (CB Scheme)	E491408-A6007-CB-1	IEC62368-1:2014 2nd Edition
Audio/Video, information and communication technology equipment - Part 1: Safety requirements (LVD)	E491408-A0007-CB-1	EN62368-1:2014 + A11:2017
Household and similar electrical appliances - Safety - Part 1: General requirements	1,004,000,000,400	IEC60335-1:2010 + A2:2016 + C1:2016, 5th Edt EN60335-1:2012 + A13:2017
Measurement methods for electromagnetic fields of household appliances and similar apparatus with regard to human exposure	- LCS190308001CS	EN62233:2008
Safety of power transformers, power supplies, reactors and similar products for supply voltages up to 1100 V (CB Scheme)		IEC61558-1:2005 2nd Edition + A1:2009
Safety of power transformers, power supplies, reactors and similar products for supply voltages up to 1100 V Part 2: Particular requirements (CB Scheme)	50220402 001	IEC61558-2-16:2009 1st Edition + A1:2013
Safety of power transformers, power supplies, reactors and similar products for supply voltages up to 1100 $\mbox{\ensuremath{V}}$	50230493 001	EN61558-1:2005 + A1:2009
Safety of power transformers, power supplies, reactors and similar products for supply voltages up to 1100 V Part 2: Particular requirements		EN61558-2-16:2009 + A1:2013
EAC	RU-AT.03.67361	TP TC 004/201
RoHS2		RoHS-2011/65/EU + AM-2015/863
EMC Compliance	Conditions	Standard / Criterio
Low-voltage power supplies DC output - Part 3: Electromagnetic compatibility		EN61204-3: 2018, Class I
Electromagnetic compatibility of multimedia equipment - Emission requirements (11)		EN55032:2015, Class I
Electromagnetic compatibility - Requirements for household appliances, electric tools and similar apparatus - Part 1: Emission		EN55014-1:2006 + A2:201
Information technology equipment - Immunity characteristics - Limits and methods of measurement		EN55024:2010 + A1:201
Electromagnetic compatibility - Requirements for household appliances, electric tools and similar apparatus - Part 2: Immunity		EN55014-2:201
ESD Electrostatic discharge immunity test	Air: ±2, 4, 8kV Contact: ±2, 4kV	EN61000-4-2: 2009, Criteria I
Radiated, radio-frequency, electromagnetic field immunity test	10V/m, 80MHz-1GHz 3V/m, 1.4GHz-2GHz 1V/m, 2GHz-2.7GHz	EN61000-4-3: 2006 + A1, 2009, Criteria A
Fast Transient and Burst Immunity	AC and DC Port: ±2kV	EN61000-4-4: 2012, Criteria I
Surge Immunity	AC In Port (L-N): ±1kV DC Output Port: ±0.5kV	EN61000-4-5: 2014 +A1:2017, Criteria E
Immunity to conducted disturbances, induced by radio-frequency fields	AC and DC Port: 10V	EN61000-4-6: 2014, Criteria A
Power Magnetic Field Immunity	50Hz, 30A/m	EN61000-4-8: 2010, Criteria
Voltage Dips and Interruptions	Voltage Dips: 30% Voltage Dips: 60% Voltage Dips: 100% Interruptions: >95%	EN61000-4-11:2004 + A1:2017, Criteria EN61000-4-11:2004 + A1:2017, Criteria EN61000-4-11:2014 + A1:2017, Criteria EN61000-4-11: 2014 + A1:2017, Criteria
Voltage Fluctuations and Flicker in Public Low-Voltage Systems <=16A per phase		EN61000-3-3: 201:
		FCC 47 CFR Part 15 Supbart B, Class
Limitations on the amount of electromagnetic interference allowed from digital and electronic devices		1 00 17 OFFIT AFT TO CUPBART B, CIACO

Notes:

Note11: If output is connected to GND, please contact RECOM tech support for advice




Series

Specifications (measured @ Ta= 25°C, nom. Vin, full load and after warm-up unless otherwise stated)

DIMENSION AND PHYSICAL CHARACTERISTICS			
Parameter	Туре	Value	
	case, baseplate	black plastic, (UL94V-0)	
Material	potting	silicone, (UL94V-0)	
	PCB	FR4, (UL94V-0)	
Dimension (LxWxH)		31.7 x 26.7 x 21.8mm	
Weight		31.5g typ.	

Dimension Drawing (mm)




Top View


90

70

01

05





Ø0.80+0.10 / -0.05

PACKAGING INFORMATION		
Parameter	Туре	Value
Packaging Dimension (LxWxH)	tube	466.0 x 30.4 x 29.3mm
Packaging Quantity	tube	12pcs
Storage Temperature Range		-40°C to +85°C
Storage Humidity	non-condensing	20% to 90% RH max.

The product information and specifications may be subject to changes even without prior written notice. The product has been designed for various applications; its suitability lies in the responsibility of each customer. The products are not authorized for use in safety-critical applications without RECOM's explicit written consent. A safety-critical application where a failure may reasonably be expected to endanger or cause loss of life, inflict bodily harm or damage property. The applicant shall indemnify and hold harmless RECOM, its affiliated companies and its representatives against any damage claims in connection with the unauthorized use of RECOM products in such safety-critical applications.