Features

- Wide input range 85-305VAC
- Operating temperature range: -40°C to +80°C
- High efficiency over entire load range
- No external components necessary

Regulated Converter

- Household certification IEC/EN60335
 Overvoltage category OVCIII (IEC62477-1)
- 140% Peak load capability

Description


The RAC10-K/277 series are highly efficient PCB-Mount power conversion modules with ultra-low energy losses even in light load conditions. Built for worldwide usage, the AC/DC units cover an enhanced mains input range of 85VAC up to 305VAC and come with international safety certifications for both industrial and household standards. These AC/DC modules offer fully protected single or dual outputs as well as EMC Class B compliance without the need of any external components. The 140% peak power capability makes the RAC10-K/277 series suitable for inductive, high start-up current or nonlinear loads. With a full load temperature range of -40°C to +65°C, they are ideal for always-on and standby mode operations in process automation, IoT and smart building applications.

Selection Guid	е				
Part Number	Input Voltage Range [VAC]	Output Voltage [VDC]	Output Current [mA]	Efficiency typ. ⁽¹⁾ [%]	Max. Capacitive Load [µF]]
RAC10-3.3SK/277	85-305	3.3	2500	79	10000
RAC10-05SK/277	85-305	5	2000	82	8000
RAC10-12SK/277	85-305	12	840	84	1500
RAC10-15SK/277	85-305	15	670	85	1000
RAC10-18SK/277	85-305	18	560	85	800
RAC10-24SK/277	85-305	24	420	84	330
RAC10-12DK/277	85-305	±12	±420	82	±1200
RAC10-15DK/277	85-305	±15	±340	83	±1000

Notes:

Note1: Efficiency is tested at 25°C with constant resistant mode at full load and 230VAC

Model Numbering



Output Voltage —

Ordering Examples:

RAC10-05SK/277 RAC10-24SK/277 RAC10-12DK/277

10 Watt 24Vout 10 Watt 12Vout

5Vout

10 Watt

Single Output Single Output Dual Output

Single or Dual Output



RAC10-K/277

10 Watt 2" x 1" Single and Dual Output





YOU MAY ALSO LIKE Please consider this alternatives:



UL62368-1 certified CSA C22.2 No. 62368-1-14 certified IEC/EN60950-1 certified IEC/EN60335-1 certified IEC/EN62368-1 certified EN62233 certified EN62477-1 certified EN61204-3 compliant CB-Report

RAC10-K/277 Series

Specifications (measured @ Ta= 25°C, nominal input voltage (115/230VAC), full load and after warm-up)

Parameter	Cond	Condition		Тур.	Max.
Internal Input Filter				,,,,,,,,,,,,,,,,,,,,,,,,,,,,,,,,,,,,,,,	Pi Type
Input Voltage Range (2,3)	nom. Vin-	nom. Vin= 277VAC		277VAC	305VAC 430VDC
	115	115VAC			250mA
Input Current)VAC			210mA
	277	VAC			190mA
	115	5VAC			15A
Inrush Current	230	230VAC			30A
	277	VAC			36A
No load Power Consumption				150mW	250mW
ErP Standby Mode Conformity		0.5W			0.3W
(Output Load Capability)	Input Power=	1.0W			0.7W
		2.0W	47Hz		1.4W
Input Frequency Range					63Hz
Overload Capability	peak duty cycle: 10	peak duty cycle: 10%; TAMB +50°C max.			140%/10s
Minimum Load	Sir	Single Dual			
Minimum Load	D			10%	
	115VAC		0.60		
Power Factor	230VAC		0.50		
	277VAC		0.45		
Start-up Time				30ms	
Rise Time					25ms
	115VAC			15ms	
Hold-up time	230VAC			90ms	
	277		110ms		
Internal Operating Frequency					100kHz
Output Ripple and Noise (4)	20MHz BW	3.3Vout, 5Vout others		60mVp-p	1% of Vout


Notes:


The products were submitted for safety files at AC-Input operation Note2:

Note3: Refer to "Line Derating"

Note4: Measurements are made with a 0.1µF MLCC & 10µF E-cap in parallel across output. (low ESR)

Efficiency vs. Load






continued on next page

RAC10-K/277 Series

Specifications (measured @ Ta= 25°C, nominal input voltage (115/230VAC), full load and after warm-up)






RAC10-K/277

Specifications (measured @ Ta= 25°C, nominal input voltage (115/230VAC), full load and after warm-up)

Series

REGULATIONS			
Parameter	Con	dition	Value
Output Accuracy			±1.0% typ.
Line Regulation	low line	low line to high line	
Load Regulation	0-100% load	3.3, 5Vout others	1.5% typ. 1.0% typ.
Cross Regulation	dual ou	itput only	±10.0% max.
Transient Response		step change ery time	4.0% max. 500µs

Deviation vs Load



RAC10-K/277

Series


Specifications (measured @ Ta= 25°C, nominal input voltage (115/230VAC), full load and after warm-up)

PROTECTIONS			
Parameter	-	Туре	Value
Input Fuse (5)			T2A, slow blow
Short Circuit Protection (SCP)			Hiccup, automatic restart
Over Voltage Protection (OVP)			150% - 195%, latch off mode
Over Load Protection (OLP)			150% - 195%, hiccup mode
Over Voltage Category (OVC)	according to	IEC/EN62477-1	OVC III
Class of Equipment			Class II
Isolation Voltage	tested	for 1 minute	4kVAC
Isolation Resistance	I/D to O/D	Isolation Voltage 500VDC	1GΩ min.
Isolation Capacitance	I/P to O/P	100kHz/0.1V	100pF max.
Insulation Grade		·	reinforced
Leakage Current			0.25mA max.
Notes:			
Note5: F	Refer to local safety regulations	s if input over-current protectio	n is also required


ENVIRONMENTAL				
arameter Condition			Value	
	@ natural convection 0.1m/s -		full load	-40°C to +65°C
Operating Temperature Range		refei	r to line derating	-40°C to +80°C
Maximum Case Temperature				+100°C
Temperature Coefficient				0.05%/K
Operating Altitude				3000m
Operating Humidity	non-conde	non-condensing		20% to 90% RH
Design Lifetime	115VAC/60Hz and fu	115VAC/60Hz and full load at +25°C		>194 x 10 ³ hours
MTBF	according to MIL-HDBK-217F,	GB	+25°C	>1750 x 10 ³ hours
		U.D.	+40°C	>1582 x 10 ³ hours
Pollution Degree				PD2
Vibration				10-500Hz, 2G 10min./1cycle, period 60min. each along x,y,z axes

Derating Graph

(@ Chamber and natural convection 0.1m/s)







RAC10-K/277

Series

Specifications (measured @ Ta= 25°C, nominal input voltage (115/230VAC), full load and after warm-up)

SAFETY AND CERTIFICATIONS

Audio/Video, information and communication technology equipment - Safety equirements	E224736	UL62368-1, 2nd Edition, 2014
		CAN/CSA C22.2 No. 62368-1-14, 2nd Edition, 2014
		IEC60950-1:2005, 2nd Edition + A2:2013
nformation Technology Equipment, General Requirements for Safety (LVD)	E491408-A4-CB-1	EN60950-1:2006 + A2:2013
Household and similar electrical appliances - Safety - Part 1: General equirements	LCS170821028CS	IEC60335-1:2010 + A2:2016 + C1:2016, 5th Edition EN60335-1:2012 + A11:2014
Audio/Video, information and communication technology equipment - Safety equirements (CB Scheme)	, — 16BCS10045 11	IEC62368-1:2014, 2nd Edition
Audio/Video, information and communication technology equipment - Safety equirements (LVD)	100031004311	EN62368-1:2014 + A11:2017
Measurement methods for electromagnetic fields of household appliances and similar apparatus with regard to human exposure	LCS170821028CS	EN62233:2008
Safety requirements for power electronic converter systems and equipment - Part 1: General	LCS181212006CS	IEC62477-1:2012 + A1:2016, 1st Edition EN62477-1: 2012 + A1:2017
AC Safety of Low Voltage Equipment	RU-AT.03.67361	TP TC 004/020, 2011
RoHS2		RoHS 2011/65/EU + AM2015/863
MC Compliance (7)	Conditions	Standard / Criterion
.ow-voltage power supplies DC output - Part 3: Electromagnetic compatibilit	y	EN61204-3:2000, Class B
nformation technology equipment - Radio disturbance characteristics	LCS170821088AE	AS/NZS CSPR 22:2009 + A1:2010, Class B
SD Electrostatic discharge immunity test	±8kV Air; ±4kV Contact	EN61000-4-2: 2009, Criteria B
Radiated, radio-frequency, electromagnetic field immunity test	10V/m, 80MHz-1GHz 3V/m, 1.5GHz-2GHz 1V/m, 2GHz-2.7GHz	EN61000-4-3: 2006 + A2, 2010, Criteria A
Fast Transient and Burst Immunity	AC In Port: ±2.0kV DC Out Port: ±2.0kV	EN61000-4-4:2012, Criteria B
Surge Immunity	AC In Port: ±1.0kV L-PE, N-PE ±2.0kV DC Out Port: ±0.5kV	EN61000-4-5:2014, Criteri B
mmunity to conducted disturbances, induced by radio-frequency fields	10Vrms	EN61000-4-6:2014, Criteria A
Power Magnetic Field Immunity	50Hz, 1A/m	EN61000-4-8:2010, Criteria A
/oltage Dips and Interruptions	Voltages Dips: >95% Voltage Dips: 30% Interruptions: >95%	EN61000-4-11: 2004, Criteria B EN61000-4-11: 2004, Criteria C EN61000-4-11: 2004, Criteria C
/oltage Fluctuations and Flicker in Public Low-Voltage Systems <=16A per phase		EN61000-3-3: 2013


Note7: If output is connected to GND, please contact RECOM tech support for advice

Parameter	Туре	Value
	case	black plastic (UL94V-0)
Matarial	potting	silicone (UL94V-0)
Material	PCB	FR4 (UL94V-0)
	baseplate	plastic (UL94V-0)
Dimension (LxWxH)		52.5 x 27.4 x 23.0mm
Weight		65g typ.

RAC10-K/277

Specifications (measured @ Ta= 25°C, nominal input voltage (115/230VAC), full load and after warm-up)

Series



PACKAGING INFORMATION				
Parameter	Туре	Value		
Packaging Dimension (LxWxH)	tube	490.0 x 56.0 x 40.0mm		
Packaging Quantity		15pcs		
Storage Temperature Range		-40°C to +85°C		
Storage Humidtiy	non-condensing	20% to 90% RH		

The product information and specifications may be subject to changes even without prior written notice. The product has been designed for various applications; its suitability lies in the responsibility of each customer. The products are not authorized for use in safety-critical applications without RECOM's explicit written consent. A safety-critical application is an application where a failure may reasonably be expected to endanger or cause loss of life, inflict bodily harm or damage property. The applicant shall indemnify and hold harmless RECOM, its affiliated companies and its representatives against any damage claims in connection with the unauthorized use of RECOM products in such safety-critical applications.