

# RAC20NE-K/277/EPID Series ◊ AC/DC Power Supply

20W / Input: 100V-277VAC


## FEATURES

- 85-305VAC wide input range
- Full load power ratings to 55°C
- 23 Watt Boost Power
- Optional CV/CC overcurrent limited
- EN55032 “B”: O/P either floating or earth referenced
- Surge immunity 2kVAC: L-N &; 4kV: L; N - Earth
- OVC III over voltage category up to 3000m
- Tool free push in terminals: up to 2.5mm<sup>2</sup> wires
- DIN-Rail or screw mountable
- IP40 ingress protected
- 3 year warranty



83.0 x 26.4 x 29.5mm (3.2 x 1.0 x 1.1 inch)  
70.6g (0.15 lbs)

## APPLICATIONS



## SAFETY & EMC



## DESCRIPTION

RAC20NE-K/277/EPID, power supplies are shaped to flexibly fit into different mounting conditions, regardless of whether back panel mounting with screws or clipping onto DIN rails is required. Apart from the push-in terminals for tool-free connection of wire cross-sections of up to 2.5mm<sup>2</sup>, the modules are IP40 ingress protected. Despite their extremely compact design, the class II units offer increased resistance to surges up to 2kV L-N and 4kV to earth as well as EMI-interference filters to withstand EN55032 Class “B” requirements under floating and earth reference load conditions such as PELV. Fully certified to safety standards UL/IEC/EN62368, IEC61347, IEC61558 and EN60335 with overvoltage category OVC III for worldwide nominal input voltages 100-277 VAC under full load from -40°C to 55°C or with power limitation up to 85°C, constant regulated output voltage from 5V to 36Vdc are available, and CV with constant current overload limitation protection is available as an option.

## SELECTION GUIDE (CONSTANT VOLTAGE OPERATION)

Part Number	Input Voltage Range [VAC]	Output Voltage [VDC]	Output Current nom. [mA]	Boost Current max <sup>(1)</sup> [mA]	Efficiency <sup>(2)</sup>	Output Power continuous [W]
					typ. [%]	
RAC20NE-05SK/277/EPID	85-305	5	3000	4600	86	15
RAC20NE-12SK/277/EPID	85-305	12	1667	1916	87	20
RAC20NE-24SK/277/EPID	85-305	24	833	1150	87	20
RAC20NE-36SK/277/EPID	85-305	36	555	638	88	20

## SELECTION GUIDE (CONSTANT CURRENT OPERATION)

Part Number	Input Voltage Range [VAC]	Output Voltage nom. [VDC]	Output Current rated [mA]	Efficiency <sup>(2)</sup>	Output Power continuous [W]
				typ. [%]	
RAC20NE-24SK/277/CC/EPID	85-305	24	833	87	20


Note1: Refer to „Boost Power Duty Cycle“

Note2: Efficiency is tested at 230VAC and full load at +25°C ambient

# RAC20NE-K/277/EPID Series ◊ AC/DC Power Supply

20W / Input: 100V-277VAC

## Model Numbering



Note3: add suffix "/CC" for constant current operation  
without suffix= standard constant voltage operation

## BASIC CHARACTERISTICS (measured @ T<sub>AMB</sub>= 25°C, nom. V<sub>IN</sub>, full load and after warm-up unless otherwise stated)



Parameter	Condition	Min.	Typ.	Max.
Nominal Input Voltage	50/60Hz	100VAC		277VAC
Operating Range <sup>(4)</sup>	47-63Hz	85VAC		305VAC
Input Current	115/230/277VAC			450mA
Inrush Current	cold start at 25°C	115VAC		20A
		230VAC		40A
		277VAC		50A
No Load Power Consumption				100mW
Ecodesign Standby Mode Use (Available output power for stated input power)	P <sub>IN</sub> = 0.5W	0.34W		
	P <sub>IN</sub> = 1.0W	0.74W		
	P <sub>IN</sub> = 2.0W	1.6W		
Input Frequency Range	AC Input	47Hz		63Hz
Minimum Load		0%		
Power Factor			0.6	
Start-up time				150ms
Rise time		40ms		
Hold-up time	230VAC	50ms		
Internal Operating Frequency				150kHz
Output Ripple and Noise <sup>(5)</sup>	20MHz BW			1% V <sub>out</sub>

Note4: The products were submitted to all safety files at AC-operation (90-305VAC).

Note5: Measurements are made with a 0.1µF MLCC & 10µF E-cap in parallel across output (low ESR)



The test setup can have an impact on ripple noise values (placement of scope probe, capacitors, it's specifications, wires, PCB tracks, distances, etc.)

### 5V<sub>out</sub>



**BASIC CHARACTERISTICS** (measured @  $T_{AMB} = 25^{\circ}\text{C}$ , nom.  $V_{IN}$ , full load and after warm-up unless otherwise stated)

others





**REGULATIONS** (measured @  $T_{AMB} = 25^{\circ}\text{C}$ , nom.  $V_{IN}$ , full load and after warm-up unless otherwise stated)

Parameter	Condition	Value
Output Accuracy		$\pm 2.0\%$ max.
Line Regulation	low line to high line, full load	$\pm 1.0\%$ max.
Load Regulation <sup>(6)</sup>	10% to 100% load	2.0% max.
Transient Response	25% load step change	4.0% max.
	recovery time	500 $\mu\text{s}$ typ.



Note6: Operation below 10% load will not harm the converter, but specifications may not be met

Deviation vs. Load



**REGULATIONS** (measured @  $T_{AMB} = 25^{\circ}\text{C}$ , nom.  $V_{IN}$ , full load and after warm-up unless otherwise stated)


### Deviation vs. Load



**PROTECTIONS** (measured @  $T_{AMB} = 25^{\circ}\text{C}$ , nom.  $V_{IN}$ , full load and after warm-up unless otherwise stated)

Parameter	Type		Value
Input Fuse	internal		T2A, slow blow type
Short Circuit Protection (SCP)	below 100m $\Omega$		hiccup mode; auto recovery
Over Current Protection (OCP)	"/277/EPID" versions		120% - 150%, hiccup mode
	"/277/CC/EPID" version; refer to „Output Voltage vs. Output Current“		constant current limitation until hiccup mode
Over Voltage Protection (OVP)			120% - 180%, latch off mode
Over Voltage Category (OVC)	according to 62368-1, 60335-1, 61558, 61347		OVC III (3000m)
	according to 62368-1, 60335-1, 61558		OVC II (5000m)
Over Temperature Protection (OTP)			hiccup mode; auto recovery
Class of Equipment			Class II
Isolation Voltage	I/P to O/P	1 minute	according to 61558
			according to 62368-1
Insulation Grade	I/P to O/P		reinforced

### Output Voltage vs. Output Current



# RAC20NE-K/277/EPID Series ◊ AC/DC Power Supply

## 20W / Input: 100V-277VAC


**ENVIRONMENTAL (measured @ T<sub>AMB</sub> = 25°C, nom. V<sub>IN</sub>, full load and after warm-up unless otherwise stated)**

Parameter	Condition		Value
Operating Ambient Temperature Range	@ natural convection (0.1m/s)	refer to „Derating Graph“	-40°C to +85°C
Maximum Case Temperature			+95°C
Temperature Coefficient			±0.05%/K
Operating Altitude (7)	according to 62368-1, 60335-1, 61558		5000m (OVC II)
	according to 62368-1, 60335-1, 61558, 61347		3000m (OVC III)
Operating Humidity			95% RH max.
Pollution Degree			PD2
MTBF	according to MIL-HDBK-217, G.B.	T <sub>AMB</sub> = +25°C	1190 x 10 <sup>3</sup> hours
Design Lifetime	full load	T <sub>AMB</sub> = +25°C	130 x 10 <sup>3</sup> hours

Note7: Recognized by safety agency for safe operation up to 5000m. High altitude operation may impact the performance and lifetime. Please contact RECOM tech support for advice

### Derating Graph for continuous loads


(@ Chamber, any orientation and natural convection 0.1m/s)



**BOOST POWER DUTY CYCLE (EXCEPT "/CC" MODELS)**

- P<sub>rated</sub> = refer to „Derating Graph“ [W]
- P<sub>Boost</sub> = Boost power (≤23W) [W]
- P<sub>r</sub> = recovery output power [W]
- t<sub>1</sub> = Boost time set (20s max.) [s]
- t<sub>2</sub> = recovery time (min. 2 x t<sub>1</sub>) [s]

$$P_r = \frac{P_{rated} \times (t_1 + t_2) - (P_{Boost} \times t_1)}{t_2}$$



#### Practical Example (RAC20NE-05SK/277/EPID):

Take the RAC20NE-05SK/277/EPID at 230VAC input voltage and full load at T<sub>AMB</sub> = 80°C, with natural convection.

P<sub>rated</sub> = 10W  
 P<sub>Boost</sub> = 23W  
 t<sub>1</sub> = 20s  
 t<sub>2</sub> = 50s

$$P_r = \frac{10W \times (20s + 50s) - (23W \times 20s)}{50s} = 4.8W$$

# RAC20NE-K/277/EPID Series ◊ AC/DC Power Supply

20W / Input: 100V-277VAC



## SAFETY & CERTIFICATIONS

Certificate Type (Safety)	Report Number	Standard
Audio/Video, information and communication technology equipment - Part1: Safety requirements 3rd Edition	E491408-A6034-UL	UL62368-1:2019 3rd Edition
		CAN/CSA-C22.2 No. 62368-1-19 3rd Edition
Audio/Video, information and communication technology equipment - Part1: Safety requirements 3rd Edition	240408022	IEC62368-1:2018 3rd Edition
		EN IEC 62368-1:2020+A11:2020
Audio/Video, information and communication technology equipment - Part1: Safety requirements 3rd Edition	085-240223001-000	IEC62368-1:2018 3rd Edition
		EN IEC 62368-1:2020+A11:2020
Audio/Video, information and communication technology equipment - Part1: Safety requirements 3rd Edition	085-240223401-000	IEC62368-1:2018 3rd Edition
		EN IEC 62368-1:2020+A11:2020
Household and similar electrical appliances – Safety – Part 1: General requirements	64.110.24.02233.01	IEC60335-1:2010 + C1:2016 5th Edition
		EN60335-1:2012 + A15:2021
Measurement methods for electromagnetic fields of household appliances and similar apparatus with regard to human exposure	64.110.24.02233.01	EN62233:2008
Safety of power transformers, power supplies, reactors and similar products for supply voltages up to 1100 V 3rd Edition	085-240223101-000	IEC61558-1:2017 3rd Edition
		EN IEC 61558-1:2019
Safety of power transformers, power supplies, reactors and similar products for supply voltages up to 1100 V Part 2: Particular requirements	085-240223101-000	IEC61558-2-16:2009+A1:2013 1st Edition
		EN61558-2-16:2009+A1:2013
Lamp controlgear Part 1: General and safety requirements	085-240223201-000	IEC61347-1:2015+A1:2017 3rd Edition
		EN61347-1:2015+A1:2021
Lamp controlgear Part 2-13: Particular requirements for d.c. or a.c. supplied electronic controlgear for LED modules	085-240223201-000	IEC61347-2-13:2014+A1:2016 2nd Edition
		EN61347-2-13:2014+A1:2017

EMC Compliance according to EN IEC61204-3	Condition	Standard / Criterion
Low voltage power supplies, d.c. output Part 3: Electromagnetic compatibility (EMC)		EN IEC 61204-3:2018
ESD Electrostatic discharge immunity test	Air: ±2, 4, 8kV	IEC61000-4-2:2008, Criteria A EN61000-4-2:2009, Criteria A
	Contact: ±6kV for all versions except 5Vout version Contact: ±4kV for all versions except 5Vout version	
Radiated, radio-frequency, electromagnetic field immunity test	10V/m (80-1000MHz), 3V/m (1400-2000MHz), 1V/m (2000-2700MHz)	IEC/EN61000-4-3:2006 + A2:2010 Criteria A
Fast Transient and Burst Immunity	L, N, L-N ±2kV for 24V and 36Vout versions	IEC/EN61000-4-4:2012, Criteria A
	L, N, L-N ±2kV for 5V and 12Vout versions	IEC/EN61000-4-4:2012, Criteria B
	L, N, L-N ±4kV for all versions	
Surge Immunity <sup>(8)</sup>	L-N: 0.5, 1kV; for all versions; only mode 1	IEC/EN61000-4-5:2014 + A1:2017, Criteria A
	L-N: 2kV; for all versions; only mode 1	IEC/EN61000-4-5:2014 + A1:2017, Criteria B
	L-PE, N-PE: 1, 2kV; for all versions; only mode 1	IEC/EN61000-4-5:2014 + A1:2017, Criteria A
	L-PE: 4kV; for all versions; only with mode 2	IEC/EN61000-4-5:2014 + A1:2017, Criteria B
	N-PE: 4kV; for all versions; only with mode 2	IEC/EN61000-4-5:2014 + A1:2017, Criteria A
Immunity to conducted disturbances, induced by radio-frequency fields	10Vrms (0.15-80MHz)	IEC61000-4-6:2013, Criteria A EN61000-4-6:2014, Criteria A
Power Magnetic Field Immunity	30A/m	IEC61000-4-8:2009 / EN61000-4-8:2010
Voltage Dips and Interruptions	Dips: 100% (0.5P, 1.0P), 60%, 30%, 20%	IEC/EN61000-4-11:2004+A1:2017, Criteria A
	Interruption: 100%	IEC/EN61000-4-11:2004+A1:2017, Criteria B
Limits of Voltage Fluctuations & Flicker		EN61000-3-3:2013+A1:2019





EMC Compliance according to EN55032	Condition	Standard / Criterion
Electromagnetic compatibility of multimedia equipment – Emission Requirements	O/P either floating or connected to GND	EN55032:2015+A11:2020

Note8: Mode1: O/P did not connect to GND  
Mode2: O/P connected to GND

### DIMENSION & PHYSICAL CHARACTERISTICS

Parameter	Type	Value
Materials	case/baseplate	plastic, (UL94 V-0)
	potting	silicone, (UL94 V-0)
	PCB	FR4, (UL94 V-0)
Dimension (LxWxH)		83.0 x 26.4 x 29.5mm 3.2 x 1.0 x 1.1 inch
Weight		70.6g typ. 0.15 lbs

### Dimension Drawing (mm)



### Connector Information

#### AC Input (CON1)

#	Function	Wire cross section <sup>(9)</sup>
1	VAC in (L)	20-12 AWG (0.2-2.5mm <sup>2</sup> )
3	VAC in (N)	Usable wire: solid/stranded

#### DC Output (CON2)

#	Function	Wire cross section <sup>(9)</sup>
3	+Vout	20-12 AWG (0.2-2.5mm <sup>2</sup> )
4	-Vout	Usable wire: solid/stranded

FC= Fixing centers

Note9: Min. Wire cross section are suggested values only, and need to be aligned with the applicable safety regulation. No ferrules required for stranded wires when tool-less pushing in is not suggested.


Note10: For DIN-Rail mounting, follow the instructions under „Mounting Instruction“

Tolerance: xx.x= ±0.5mm  
xx.xx= ±0.25mm


### INSTALLATION & APPLICATION

#### Mounting Instruction

Mounting Rail: Standard TS35 DIN Rail in accordance with EN 60715




#### Installation Instruction <sup>(11)</sup>



Note11: Panel mount installations can be realized in any orientation. No distance to adjacent components is required for thermally effective contact. In pure convection cooled ambient at least two of four long sides shall have access to air convection (eg 2cm distance)



### BLOCK DIAGRAMM



### PACKAGING INFORMATION

Parameter	Type	Value
Packaging Dimension (LxWxH)	box	365.0 x 210.0 x 46.0mm
Packaging Quantity		22pcs
Storage Temperature Range		-40°C to +90°C
Storage Humidity		95% RH max.

The product information and specifications may be subject to changes even without prior written notice. The product has been designed for various applications; its suitability lies in the responsibility of each customer. The products are not authorized for use in safety-critical applications without RECOM's explicit written consent. A safety-critical application is an application where a failure may reasonably be expected to endanger or cause loss of life, inflict bodily harm or damage property. The applicant shall indemnify and hold harmless RECOM, its affiliated companies and its representatives against any damage claims in connection with the unauthorized use of RECOM products in such safety-critical applications.