

FEATURES

- 6 Watt output up to 60°C
- 1"x1" footprint; 17mm low profile
- 100-277VAC nominal operating range
- -40°C to +90°C operating temperature ratings
- OVC III rated up to 5000m Altitude
- 2MOPP rating; BF ready
- EN55032 class "B" compliant @ floating load
- 3 years warranty



Dimensions (LxWxH): 25.4 x 25.4 x 16.7mm (1.0 x 1.0 x 0.6 inch) 20g (0.04 lbs)

APPLICATIONS































DESCRIPTION

The industry's most compact integrated 6-watt AC/DC power supply series RACM06E is based on a 1"x1" footprint and fits into a low profile of just 17mm. Multiple international safety certifications to industrial, medical, and household standards ease implementation into a wide range of applications for direct connections to worldwide mains input voltage conditions to OVC III and without limitation to operating altitudes of up to 5000m. Even though it is a cost-efficient construction the thermally optimized design has safety rating for full load output power from -40°C up to 60°C with some derating continuing up 90°C. Internal EMI Filter supports compliance to EN55032 class "B" in floating output configurations without any need for additional filter components.

SELECTION GUIDE					
Part Number	Input Voltage Range [VAC]	Output Voltage nom. [VDC]	Output Current max. [mA]	Efficiency ⁽¹⁾ typ. [%]	Output Power max. [W]
RACM06E-3.3SK/277	80-305	3.3	1818	73	6
RACM06E-05SK/277	80-305	5	1200	77	6
RACM06E-12SK/277	80-305	12	500	82	6
RACM06E-15SK/277	80-305	15	400	83	6
RACM06E-24SK/277	80-305	24	250	83	6

Note1: Efficiency is tested at nominal input (230VAC) and full load at +25°C ambient

Rev 1-2024





BASIC CHARACTERISTICS (measure	ed @ T _{AMB} = 25°C, nom. V _{IN}	, full load and after warm-up unless other	wise stated)		
Parameter	Condition			Тур.	Max.
Nominal Input Voltage		50/60Hz			277VAC
Operating Range (2)		47-63Hz	80VAC		305VAC
——————————————————————————————————————		DC	120VDC		430VDC
Input Current		115/230/277VAC			150mA
		115VAC			15A
Inrush Current	cold start at 25°C	230VAC			30A
		277VAC			36A
No Lond Dower Consumption	RACM06E-	3.3SK/277; RACM06E-24SK/277			110mW
No Load Power Consumption		others			120mW
Input Frequency Range					63Hz
Minimum Load			0%		
			0.6		
Power Factor			0.5		
			0.48		
0				25ms	
Start-up time				20ms	
	RACM06E-15SK/277				15ms
Rise time				22ms	
				10ms	
		RACM06E-3.3SK/277; RACM06E-05SK/277	50ms		
Hold-up time	230VAC	others	60ms		
Internal Operating Frequency					130kHz
		RACM06E-3.3SK/277			120mVp-p
Output Ripple and Noise (3)	20MHz BW	RACM06E-05SK/277			100mVp-p
	others				1% Vout

Note2: The products were submitted for safety files at AC-Input operation.

Note3: Measurements are made with a 0.1µF MLCC & 10µF E-cap in parallel across output. (low ESR)

RACM06E-3.3SK/277; RACM06E-05SK/277









BASIC CHARACTERISTICS (measured @ T_{AMB}= 25°C, nom. V_{IN}, full load and after warm-up unless otherwise stated)

others






REGULATIONS (measured @ T _{AMB} = 25°C, nom. V _{IN} , full load and after warm-up unless otherwise stated)			
Parameter	Condition	Value	
Output Accuracy		±2.0% max.	
Line Regulation	low line to high line, full load	±0.3% max.	
Load Regulation (4)	10% to 100% load	1.0% max.	
Transient Response	25% load step change	4.0% max.	
	recovery time	500μs typ.	

Note4: Operation below 10% load will not harm the converter, but specifications may not be met

Deviation vs. Load






PROTECTIONS (measured @ T _{AMB} = 25°C, nom	. V _{IN} , full load and after v	varm-up unless otherwi	ise stated)
Parameter	Ту	/pe	Value
Input Fuse (6)	refer to "Prote	ection Circuit"	external fuse required
Short Circuit Protection (SCP)	below	100mΩ	hiccup mode
Over Voltage Protection (OVP)			125% - 195%, hiccup mode
Overal Veltage Catagorius (OVO)	according to 60	601-1, 60335-1	OVCII
Over Voltage Category (OVC)	according to 62368-1, 61558		OVCIII
Over Temperature Protection (OTP)			not protective against overload, hiccup mode
Class of Equipment			Class II
location Voltage (5)	I/P to O/P; 1 minute	according to 61558	4.2kVAC
Isolation Voltage (5)		according to 62368-1	6kVDC
Insulation Grade			reinforced
Leakage Current			0.1mA max.
Means of Protection			2MOPP
Medical Device Classification			designed to support type BF applied part

Note5: For repeat Hi-Pot testing, reduce the time and/or the test voltage Note6: Safety agency tested fuses: T1A, 420VAC or T1A, 600VAC

Protection Circuit (6)



ENVIRONMENTAL (measured @ T _{AN}	$_{\rm B}$ = 25°C, nom. $V_{\rm IN}$, full load and afte	r warm-up unless otherwise stated)	
Parameter	Condition		Value
Operating Ambient Temperature Range	@ natural convection (0.1m/s); with derating		-40°C to +90°C
Maximum Case Temperature			+110°C
Temperature Coefficient			±0.05%/K
Operating Altitude (7)	according to 62368-1, 60601-1, 61558		5000m
Operating Humidity	non-condensing		90% RH max.
Pollution Degree			PD2
MTBF	according to MILLIDDI/ 017 CD	T _{AMB} = +25°C	1936 x 10 ³ hours
	according to MIL-HDBK-217, G.B.	T _{AMB} = +40°C	1653 x 10 ³ hours
Design Lifetime	T _{AMB} = +50°C		43 x 10 ³ hours


Note7: Recognized by safety agency for safe operation up to 5000m. High altitude operation may impact the performance and lifetime. Please contact RECOM tech support for advice





ENVIRONMENTAL (measured @ T_{AMB}= 25°C, nom. V_{IN}, full load and after warm-up unless otherwise stated)

Derating Graph

(@ Chamber and natural convection 0.1m/s)







SAFETY & CERTIFICATIONS		
Certificate Type (Safety)	Report Number	Standard
Audio/Video, information and communication technology equipment - Part1: Safety requirements 2nd Edition (LVD)	64.210.22.05225.01	EN62368-1:2014+A11:2017
Audio/Video, information and communication technology equipment - Part1: Safety requirements 3rd Edition (CB)	- 085-220522401-000	IEC62368-1:2018 3rd Edition
Audio/Video, information and communication technology equipment - Part1: Safety requirements 3rd Edition	- 085-220522401-000	EN IEC 62368-1:2020+A11:2020
Medical electrical equipment Part 1: General requirements for basic safety and essential performance	E314885	ANSI/AAMI ES60601-1:2005 + A2:2010 CAN/CSA-C22.2 No. 60601-1:14 3rd Edition
Medical electrical equipment Part 1: General requirements for basic safety and essential performance (CB)	00000010000 00701	IEC60601-1:2005 + AM1:2012 3rd Edition
Medical electrical equipment Part 1: General requirements for basic safety and essential performance	22SBDS12050-00721	EN60601-1:2006 + A12:2014
Household and similar electrical appliances – Safety – Part 1: General requirements	C4 000 00 05007 01	IEC60335-1:2010 + C1:2016 5th Edition EN60335-1:2012 + A15:2021
Measurement methods for electromagnetic fields of household appliances and similar apparatus with regard to human exposure	64.260.22.05227.01	EN62233:2008+AC:2008



ow / omvorodimpat roov 277 vito		
SAFETY & CERTIFICATIONS		
Safety of power transformers, power supplies, reactors and similar products for supply voltages up to 1100 V 3rd Edition (CB)	085-220522601-000	IEC61558-1:2017 3rd Edition
Safety of power transformers, power supplies, reactors and similar products for supply voltages up to 1100 V 3rd Edition (LVD)	64.250.22.05226.01	EN IEC 61558-1:2019
Safety of power transformers, power supplies, reactors and similar products for supply voltages up to 1100 V Part 2: Particular requirements (CB)	085-220522601-000	IEC61558-2-16:2009 + A1:2013 1st Edition
Safety of power transformers, power supplies, reactors and similar products for supply voltages up to 1100 V Part 2: Particular requirements (LVD)	64.250.22.05226.01	EN61558-2-16:2009+A1:2013
RoHS2		RoHS 2011/65/EU + AM2015/863
FMC Compliance (FMCOCOL 1 2)	Condition	Standard / Critorian
EMC Compliance (EN60601-1-2) Medical electrical equipment Part 1-2: General requirements for basic safety	Condition	Standard / Criterion
and essential performance		EN60601-1-2:2015 + A1:2021
ESD Electrostatic discharge immunity test	Air: ±2, 4, 8, 15kV Contact: ±8kV	EN61000-4-2:2009
Radiated, radio-frequency, electromagnetic field immunity test	10V/m (80-2700MHZ); 27V/m (385MHz); 28V/m (450MHz); 9V/m (710, 745, 780MHz); 28V/m (810, 870, 930MHz); 28V/m (1720, 1845, 1970MHz); 28V/m (2450MHz); 9V/m (5240, 5500, 5785MHz)	EN61000-4-3:2006 + A2:2010
Fast Transient and Burst Immunity	AC Port: L-N: 2kV	EN61000-4-4:2012
	AC Port: L-N: 0.5, 1kV	
Surge Immunity	AC Port: L-N: 2kV, with external filter	EN61000-4-5:2014 + A1:2017
	refer to "External filter"	
Immunity to conducted disturbances, induced by radio-frequency fields	3.6Vrms (0.15-80MHz)	EN61000-4-6:2014
Power Magnetic Field Immunity	30A/m	EN61000-4-8:2010
Voltage Dips and Interruptions	Dips: 100% (0.5P, 1.0P), 30% Interruptions: 100%	EN61000-4-11:2004 + A1:2017
Limits of Voltage Fluctuations & Flicker	JYTA-R01-2200312	EN61000-3-3:2013 + A1:2019
EMC Compliance (EN61204-3)	Condition	Standard / Criterion
Low voltage power supplies, d.c. output Part 3: Electromagnetic compatibility		EN IEC 61204-3:2018
ESD Electrostatic discharge immunity test	Air: ±2, 4, 8kV Contact: ±4kV	EN61000-4-2:2009, Criteria A
Radiated, radio-frequency, electromagnetic field immunity test	10V/m (80-1000MHz) 3V/m (1400-2000MHz) 1V/m (2000-2700MHz)	EN61000-4-3:2006 + A2:2010, Criteria A
Fast Transient and Burst Immunity	AC Port: L-N: 2kV	EN61000-4-4:2012, Criteria A
Surge Immunity	AC Port: L-N: 1kV	EN61000-4-5:2014 + A1:2017, Criteria A
Immunity to conducted disturbances, induced by radio-frequency fields	10Vrms (0.15-80MHz)	EN61000-4-6:2014, Criteria A
Power Magnetic Field Immunity	30A/m	EN61000-4-8:2010, Criteria A
Valtaga Dine	100% (0.5P; 1.0P), 20%, 30%	EN61000-4-11:2004 + A1:2017, Criteria A
Voltage Dips	60%	EN61000-4-11:2004 + A1:2017, Criteria B
Voltage Interruptions	100%	IEC/EN61000-4-11:2004 + A1:2017, Criteria B
Limits of Voltage Fluctuations & Flicker		EN61000-3-3:2013 + A1:2019
EMC Compliance (EN55032)	Condition	Standard / Criterion
Electromagnetic compatibility of multimedia equipment - Emission Requirements	O/P connected to GND:	EN55032:2015 + A11:2020, Class B
Limitations on the amount of electromagnetic interference allowed from digital	refer to: "PELV installation"	
and electronic devices	and floating output; without external filter	FCC 47 CFR Part 15 Subpart B, Class B


RACM06E-K/277 Series / AC-DC Power Supply

6W / Universal Input 100V-277VAC



SAFETY & CERTIFICATIONS

Suggested external circuit for 2kV surge rating




Component List

F ₁	Var₁	
20Ω, 2W	TVR1; 350VAC	

Suggested external filter for PELV installation

refer to "EMC Compliance (EN55032)"




Component List


C ₁	CMC ₁
100nF	60mH:
	RACMC60-500/UF9.8 (coming soon)


DIMENSION & PHYSICAL CHARACTERISTICS				
Parameter	Туре	Value		
	case/baseplate	plastic, (UL94-V0)		
Materials	potting	PU, (UL94-V0)		
	PCB	FR4, (UL94-V0)		
Dimension (LyMyH)		25.4 x 25.4 x 16.7mm		
Dimension (LxWxH)		1.0 x 1.0 x 0.6 inch		
Weight		20g typ.		
weight		0.04 lbs		

Dimension Drawing (mm)









Pin# Single VAC in (L) 2 VAC in (N) 4 -Vout

Pinning Information [P5b]

5 +Vout



Tolerance: $x.x = \pm 0.5$ mm $x.xx = \pm 0.25mm$ Technical Data Sheet

RACM06E-K/277 Series / AC-DC Power Supply 6W / Universal Input 100V-277VAC



PACKAGING INFORMATION				
Parameter	Туре	Value		
Packaging Dimension (LxWxH)	tube	530.0 x 27.5 x 25.6mm		
Packaging Quantity		18pcs		
Storage Temperature Range		-40°C to +90°C		
Storage Humidity	non-condensing	95% RH max.		

The product information and specifications may be subject to changes even without prior written notice. The product has been designed for various applications; its suitability lies in the responsibility of each customer. The products are not authorized for use in safety-critical applications without RECOM's explicit written consent. A safety-critical application where a failure may reasonably be expected to endanger or cause loss of life, inflict bodily harm or damage property. The applicant shall indemnify and hold harmless RECOM, its affiliated companies and its representatives against any damage claims in connection with the unauthorized use of RECOM products in such safety-critical applications.